

SRG-K CONTROL CABLES

Flexible Silicone Rubber Glass Braid Conductors with an Overall Aramid Fiber Jacket, Temp Rating 200°C, 600V



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Stranded tinned, annealed copper per ASTM B33
- Insulation:** Silicone Rubber with a fiberglass braid over the insulation
- Cabling:** Conductors are cabled with a left hand lay and bound with a polyester tape
- Jacket:** K-Fiber braid, treated with a high temperature saturant, covers the core

APPLICATIONS AND FEATURES:

Used for equipment wiring, as well as signal and control circuits. Ideal in locations where high temperature or hazardous conditions exist that require heat resistance at 600 volts.

K Fiber Jacket provides improved mechanical strength and abrasion resistance. Flexible. Good chemical strength. Excellent electrical properties. Passes IEEE 383 70,000 BTU/Hr Flame test while maintaining circuit integrity.

SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- IEEE 383 Flame Test (70,000 btu)
- RoHS-3 Complies with European Directive 2015/863

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Insul. Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	mil	inch	lb/1000ft	°C	Style/Type
C51405	10	3	45	0.555	180	200	Non-UL

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Insul. Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	mm	mm	kg/km	°C	Style/Type
C51405	10	3	1.14	14.10	268	200	Non-UL

