

## CU 2000V XLPE Insulation. RHH/RHW-2

Power Cable 2000Volt Single Conductor Copper, Cross Linked Polyethylene (XLPE) insulation RHH/RHW-2




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type RHH/RHW-2

### APPLICATIONS AND FEATURES:

Southwire's 2000 Volt power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 4
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE E32071 {UL} XXX KCMIL (XXX{mm<sup>2</sup>}) CU TYPE RHH OR RHW-2 120 MILS XLP FOR CT USE SUN. RES. VW-1 2000 VOLTS {NOM}-ANCE



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH  
SUPPORT™**

Services

UPDATED: Jan. 24, 2024, 6:19 p.m. UTC REVISION: 1.000.003

Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Strand Count   | Diameter Over Conductor | Insul. Thickness | Approx. OD | Copper Weight | Approx. Weight |
|--------------|------------|----------------|-------------------------|------------------|------------|---------------|----------------|
|              | AWG/Kcmil  | No. of Strands | inch                    | mil              | inch       | lb/1000ft     | lb/1000ft      |
| TBA          | 8          | 7              | 0.141                   | 70               | 0.281      | 50            | 74             |
| TBA          | 6          | 7              | 0.177                   | 70               | 0.317      | 81            | 109            |
| TBA          | 4          | 7              | 0.225                   | 70               | 0.365      | 128           | 161            |
| TBA          | 2          | 7              | 0.282                   | 70               | 0.422      | 204           | 244            |
| TBA          | 1          | 19             | 0.322                   | 90               | 0.502      | 258           | 318            |
| TBA          | 1/0        | 19             | 0.361                   | 90               | 0.541      | 325           | 391            |
| TBA          | 2/0        | 19             | 0.405                   | 90               | 0.585      | 410           | 482            |
| TBA          | 3/0        | 19             | 0.456                   | 90               | 0.636      | 518           | 598            |
| TBA          | 4/0        | 19             | 0.512                   | 90               | 0.692      | 653           | 741            |
| TBA          | 250        | 37             | 0.558                   | 105              | 0.768      | 771           | 884            |
| TBA          | 350        | 37             | 0.661                   | 105              | 0.871      | 1081          | 1212           |
| 568018       | 500        | 37             | 0.789                   | 105              | 0.986      | 1543          | 1748           |
| TBA          | 600        | 61             | 0.865                   | 120              | 1.105      | 1853          | 2046           |
| 648750       | 750        | 61             | 0.968                   | 120              | 1.220      | 2315          | 2569           |
| TBA          | 1000       | 61             | 1.117                   | 120              | 1.357      | 3088          | 3330           |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

| Stock Number | Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance @ 60Hz | Allowable Ampacity At 60°C | Allowable Ampacity At 75°C | Allowable Ampacity At 90°C |
|--------------|------------|--------------------|------------------|----------------------|----------------------|----------------------------|----------------------------|----------------------------|----------------------------|
|              | AWG/Kcmil  | inch               | lb               | Ω/1000ft             | Ω/1000ft             | Ω/1000ft                   | Amp                        | Amp                        | Amp                        |
| TBA          | 8          | 1.1                | 132              | 0.653                | 0.786                | 0.052                      | 40                         | 50                         | 55                         |
| TBA          | 6          | 1.2                | 209              | 0.411                | 0.495                | 0.051                      | 55                         | 65                         | 75                         |
| TBA          | 4          | 1.4                | 333              | 0.258                | 0.310                | 0.048                      | 70                         | 85                         | 95                         |
| TBA          | 2          | 1.6                | 530              | 0.162                | 0.195                | 0.045                      | 95                         | 115                        | 130                        |
| TBA          | 1          | 2.0                | 669              | 0.128                | 0.154                | 0.046                      | 110                        | 130                        | 145                        |
| TBA          | 1/0        | 2.1                | 844              | 0.102                | 0.122                | 0.044                      | 125                        | 150                        | 170                        |
| TBA          | 2/0        | 2.3                | 1064             | 0.081                | 0.097                | 0.043                      | 145                        | 175                        | 195                        |
| TBA          | 3/0        | 2.5                | 1342             | 0.064                | 0.078                | 0.042                      | 165                        | 200                        | 225                        |
| TBA          | 4/0        | 2.7                | 1692             | 0.051                | 0.062                | 0.041                      | 195                        | 230                        | 260                        |
| TBA          | 250        | 3.0                | 2000             | 0.043                | 0.053                | 0.041                      | 215                        | 255                        | 290                        |
| TBA          | 350        | 3.4                | 2800             | 0.031                | 0.039                | 0.040                      | 260                        | 310                        | 350                        |
| 568018       | 500        | 3.9                | 4000             | 0.022                | 0.029                | 0.039                      | 320                        | 380                        | 430                        |
| TBA          | 600        | 5.5                | 4800             | 0.018                | 0.025                | 0.039                      | 350                        | 420                        | 475                        |
| 648750       | 750        | 6.1                | 6000             | 0.014                | 0.022                | 0.038                      | 400                        | 475                        | 535                        |
| TBA          | 1000       | 6.7                | 8000             | 0.011                | 0.018                | 0.037                      | 455                        | 545                        | 615                        |

\* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

\* Inductive Reactance is based on non-ferrous conduit with one diameter spacing.

