

3/C CU 25KV 100% XLPE/CPE RHINOPOWER™ Type MP-GC. MSHA Approved

Class B Copper conductors, XLPE 100% Insulation Level, Copper Tape Shield, Polyvinyl Chloride (PVC) Jacket, 90°C



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded bare copper per ASTM B3 and ASTM B496
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** Cross Linked Polyethylene (XLPE) 100% and 133% Insulation Level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductors:** Two Class B compressed stranded bare copper per ASTM B3 and ASTM B8
7. **Ground Check:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 with yellow high strength, polypropylene insulation
8. **Filler:** Rubber Fillers as needed
9. **Reinforcement:** Tape and Reinforcing twine applied over the core for improved mechanical integrity and ease of stripping
10. **Jacket:** Black, mold cured, single layer, flame resistant, thermosetting Chlorinated Polyethylene (CPE). Alternate jacket colors available
11. **Reflective Stripe:** Highly visible reflective stripe embedded into the outer jacket to increase safety and help prevent cable runover (optional, contact your sales representative for part number)

APPLICATIONS AND FEATURES:

RHINOPOWER™ Type MP-GC mine power feeder cable is a heavy-duty power cable for use in stationary horizontal HV mine power distribution circuits, for permanent or semi-portable applications with power transmission in deep mines, surface mines, open pits, tunnels, in conduit or duct (not to exceed max rated voltage), and suitable for direct burial in wet or dry locations. For vertical drop requirements consult with factory application specialist.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B496 Compact Round Concentric-lay-standard copper
- ICEA S-75-381 Portable and Power Feeder Cables for Use in Mines
- MSHA Approved



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Jan. 22, 2024, 10:26 p.m. UTC REVISION: 1.000.001

SAMPLE PRINT LEGEND:

SOUTHWIRE (R) RHINO™ BRAND CABLE # AWG COMPACT CU 3/C TYPE MP-GC 25000V 100% INS. LEVEL 90°C P-07-K130025 MSHA

Table 1 – Weights and Measurements

Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Diameter Over Insulation	Ground Check Size	Ground Check Strands	Ground Check Insulation Thickness	Jacket Thickness	Approx. OD	Approx. Weight
AWG/Kcmil	No.	No.	inch	mil	inch	AWG	No.	mil	mil	inch	lb/1000ft
2	3	7	0.268	260	0.824	8	7	45	140	2.34	3300
1	3	19	0.299	260	0.855	8	7	45	140	2.42	3660
1/0	3	19	0.336	260	0.892	8	7	45	140	2.51	4080
2/0	3	19	0.376	260	0.932	8	7	45	140	2.60	4580
3/0	3	19	0.423	260	0.979	8	7	45	140	2.71	5200
4/0	3	19	0.475	260	1.031	8	7	45	140	2.89	6100
250	3	37	0.52	260	1.076	8	7	45	140	2.99	6790
300	3	37	0.57	260	1.126	8	7	45	170	3.10	7500
350	3	37	0.616	260	1.172	8	7	45	170	3.21	8360
400	3	37	0.659	260	1.215	8	7	45	170	3.33	9310
450	3	37	0.7	260	1.256	8	7	45	170	3.42	9980
500	3	37	0.736	260	1.292	8	7	45	170	3.50	10880

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance	Inductive Reactance	Working Tension	Min Bending Radius	Allowable Ampacity In Air 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	lb	inch	Amp
2	0.164	0.205	0.073	0.049	454.000	28.1	168
1	0.130	0.163	0.069	0.047	572.000	29	191
1/0	0.104	0.130	0.064	0.046	722.000	30.1	218
2/0	0.082	0.103	0.059	0.044	910.000	31.2	249
3/0	0.065	0.081	0.055	0.042	1147.000	32.5	286
4/0	0.052	0.065	0.051	0.041	1446.000	34.7	326
250	0.044	0.055	0.047	0.040	1709.000	35.9	360
300	0.037	0.046	0.044	0.039	2051.000	37.2	402
350	0.031	0.039	0.042	0.038	2393.000	38.5	439
400	0.027	0.034	0.040	0.037	2734.000	40	473
450	0.024	0.030	0.038	0.036	3075.000	41	504
500	0.022	0.028	0.037	0.036	3418.000	42	536

* Ampacities based upon ICEA S-75-381 Table I-1.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

