

600V SEOPRENE PLUS® SE00W Cord with Yellow Jacket 105°C. Silicone-Free

600 Volt, 105°C Flexible Cord. Premium Oil Resistance, Sunlight, Water Resistance and Flame Retardant, UL / CSA listed.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant TPE
3. **Filler:** Non-wicking polypropylene fillers, with a tissue-paper separator wrapped around the assembly
4. **Jacket:** Yellow TPE (other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Type SE00W Flexible Cords are permitted for indoor and outdoor temporary power uses, portable industrial machinery and compressors, food processing and washdown facilities. Type SE00W Cords are suitable for use in temperatures between -40°C to maximum 105°C.

SPECIFICATIONS:

- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- Passes CSA FT2 Flame Test
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- NEC Article 501.140 Class I Division 2

SAMPLE PRINT LEGEND:

SOUTHWIRE® SEOPRENE PLUS{TM} CORD X/C XX AWG (X.XX{mm²}) SE00W E46194 {UL} 600V -40°C TO 105°C -- CSA LL90458 SE00W 600V -50°C TO 105°C FT2 WATER RESISTANT

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 16, 2023, 11:32 p.m. UTC REVISION: 1.000.000

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
655662	18	3	16	30	60	0.363	63	7	BK/WE/GN	Yellow
598335	18	4	16	30	60	0.387	75	5	BK/WE/RD/ G	Yellow
655688	16	2	26	30	60	0.367	61	13	BK/WE	Yellow
655696	16	3	26	30	60	0.387	77	10	BK/WE/GN	Yellow
655704	16	4	26	30	60	0.416	93	8	BK/WE/GN/ R	Yellow
672272	16	5	26	30	85	0.503	131	8	BK/WE/RD/ G	Yellow
598336	14	2	41	45	80	0.497	111	18	BK/WE	Yellow
655720	14	3	41	45	80	0.522	135	15	BK/WE/GN	Yellow
655738	14	4	41	45	80	0.565	164	12	BK/WE/RD/ G	Yellow
655746	12	2	65	45	95	0.570	149	25	WE/BK	Yellow
655753	12	3	65	45	95	0.592	185	20	BK/WE/GN	Yellow
655761	12	4	65	45	95	0.642	229	16	BK/WE/RD/ G	Yellow
655787	10	3	104	45	105	0.652	244	25	BK/WE/GN	Yellow
655795	10	4	104	45	100	0.703	301	20	BK/WE/RD/ G	Yellow

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.



Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
655662	18	3	16	0.76	1.52	9.22	94	7	BK/WE/GN	Yellow
598335	18	4	16	0.76	1.52	9.83	112	5	BK/WE/RD/ G	Yellow
655688	16	2	26	0.76	1.52	9.32	91	13	BK/WE	Yellow
655696	16	3	26	0.76	1.52	9.83	115	10	BK/WE/GN	Yellow
655704	16	4	26	0.76	1.52	10.57	138	8	BK/WE/GN/ R	Yellow
672272	16	5	26	0.76	2.16	12.78	195	8	BK/WE/RD/ G	Yellow
598336	14	2	41	1.14	2.03	12.62	165	18	BK/WE	Yellow
655720	14	3	41	1.14	2.03	13.26	201	15	BK/WE/GN	Yellow
655738	14	4	41	1.14	2.03	14.35	244	12	BK/WE/RD/ G	Yellow
655746	12	2	65	1.14	2.41	14.48	222	25	WE/BK	Yellow
655753	12	3	65	1.14	2.41	15.04	275	20	BK/WE/GN	Yellow
655761	12	4	65	1.14	2.41	16.31	341	16	BK/WE/RD/ G	Yellow
655787	10	3	104	1.14	2.67	16.56	363	25	BK/WE/GN	Yellow
655795	10	4	104	1.14	2.54	17.86	448	20	BK/WE/RD/ G	Yellow

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Color Code

# of Conductor	Color Sequence
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green

