

# HVTECK CU 1/C 320NLEPR CB PVC AIA PVC 25kV 133% CSA

Single Conductor, 320 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 133% Insulation Level, Concentric Bond, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 320 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Shield:** Concentrically applied copper bond / shield wires. Complies with greater than the minimum requirement as per Table 44, CSA Standard C68.10 and Table 16A, Canadian Electrical Code Part 1
6. **Neutral Separator:** Mylar tape
7. **Inner Jacket:** PVC inner jacket
8. **Armour:** Aluminum Interlocked Armour (AIA)
9. **Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

## APPLICATIONS AND FEATURES:

Southwire's 25kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)



- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

**SAMPLE PRINT LEGEND:**  
(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CU 320 NLEPR AIA 25kV 133% INS LEVEL CB [No. x SIZE] AWG SUN  
RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Concentric Neutral | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|--------------------|------------------------|------------------|--------------------------|------------|---------------|----------------|
| AWG/Kcmil  | No.    | inch                    | inch                     | mil              | inch                            | No. x AWG          | mil                    | inch             | mil                      | inch       | lb/1000ft     | lb/1000ft      |
| 500        | 37     | 0.789                   | 1.475                    | 320              | 1.535                           | 26x14              | 110                    | 2.273            | 75                       | 2.423      | 1896          | 3815           |

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item  
1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination

Table 2 – Electrical and Engineering Data

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|----------------------------------------|--------------------------------|-----------------------------------------|
| AWG/Kcmil  | inch               | lb               | Ω/1000ft             | Ω/1000ft             | MΩ*1000ft                   | Ω/1000ft                   | Ω/1000ft                | Ω/1000ft                    | Amp                                    | Amp                            | Amp                                     |
| 500        | 29.1               | 4000             | 0.022                | 0.030                | 0.031                       | 0.047                      | 0.339 + j0.217          | 0.031 + j0.048              | 20275                                  | 616                            | 499                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

Table 3 – Weights and Measurements (Metric)

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Concentric Neutral | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|--------------------|------------------------|------------------|--------------------------|------------|---------------|----------------|
| AWG/Kcmil  | No.    | mm                      | mm                       | mm               | mm                              | No. x AWG          | mm                     | mm               | mm                       | mm         | kg/km         | kg/km          |
| 500        | 37     | 20.04                   | 37.47                    | 8.13             | 38.99                           | 26x14              | 2.79                   | 57.73            | 1.91                     | 61.54      | 2822          | 5677           |

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item  
1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination

Table 4 – Electrical and Engineering Data (Metric)

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|----------------------------------------|--------------------------------|-----------------------------------------|
| AWG/Kcmil  | mm                 | newton           | Ω/km                 | Ω/km                 | MΩ*km                       | Ω/km                       | Ω/1000ft                | Ω/1000ft                    | Amp                                    | Amp                            | Amp                                     |
| 500        | 739.14             | 17800            | 0.0722               | 0.10                 | 0.0094                      | 0.1542                     | 0.339 + j0.217          | 0.031 + j0.048              | 20275                                  | 616                            | 499                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

