

600V ROYAL® SOOW Power Cord Non-UL/CSA with Black Jacket 90°C. Silicone-Free. MSHA Approved

600 Volt, 90°C Flexible Cord. Heat, Moisture and Oil Resistant EPDM Rubber Insulation and Heat, Moisture and Oil Resistant Flexible CPE Jacket, Non UL / Non CSA.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant EPDM
3. **Filler:** Waxed paper fillers
4. **Jacket:** Black CPE (Other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Royal® Non UL/Non CSA SOOW cord is designed for use with industrial equipment, heavy tools, battery chargers, portable lights and power extensions, suitable for outdoor applications. The cable is rated -40°C to 90°C, sunlight, water, oil, and weather resistant. Southwire Type SOOW Flexible Cords are permitted for use as specified by Article 400 and related articles of the 2014 National Electrical Code.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- MSHA flame test - P07-KA070018-1MSHA
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- Federal Specification J-C-580B

SAMPLE PRINT LEGEND:

SOUTHWIRE® ROYAL® CORD X/C X AWG (X.XXmm²) SOOW 600V -40C TO 90C

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.



Table 1 – Weights and Measurements

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
		AWG/Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
558161	822521	6	5	133	45	110	0.937	702	36	BK/WE/RD/G	Black

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Table 2 – Weights and Measurements (Metric)

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
		AWG/Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
558161	822521	6	5	133	1.14	2.79	23.80	1045	36	BK/WE/RD/G	Black

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Color Code

# of Conductor	Color Sequence
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Green, Orange

