

26AWG 2 Pair Shielded Industrial Ethernet Cable

Cat 5e. CM. CMX.. 75°C. Sunlight Resistance. Outdoor Rated. RoHS-2




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 26AWG, stranded, tinned copper per ASTM B33 and B174
2. **Insulation:** High Density Polyethylene (HDPE)
3. **Pairs:** Color coded singles twisted into pairs
4. **Color Code:** 1PR - White/Green, Green; 2PR - White/Orange, Orange
5. **Assembly:** Twisted pairs cabled together with filler and wrapped with clear polyester tape to form a round cable
6. **Shielding:** An overall shield of 38 AWG tinned copper braid (75% coverage) is applied over the cable core and under a second aluminized polyester foil shield (100% coverage).
7. **Jacket:** Teal, Thermoplastic Elastomer (TPE)

APPLICATIONS AND FEATURES:

Shielded Ethernet Cat 5e cable designed for the harsh industrial environment and provides excellent protection against EMI interference. It is suitable for continuous flexing cable track and torsion applications. For use for wiring network interconnections. Industrial strength jacket provides excellent resistance to low temperatures (-40°C), common oils and chemicals, flame, UV and weather exposure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 444 Communications Cables (90°C, 300V)
- CSA C22.2 No.214 Communications cables
- RoHS-2 (European Directive 2011/65/EU)
- CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive

SAMPLE PRINT LEGEND:

Southwire Industrial Ethernet Cat 5e Flexing 2 PR 26AWG SF/UTP EXXXXXX C(UL)US TYPE CMX OUTDOOR - CM 75C SUN RES -- CE RoHS-2 -- (Lot Designator) (Sequential Footage) Made in USA



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Number of Pairs	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	Max Plug to Plug Transmission Distance + POE
	AWG/Kcmil	pair	strand	mil	mil	inch	lb/1000ft	Ω/1000ft	meter
648559	26	2	7	9	43	0.225	31.7	14	67

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

ELECTRICAL CHARACTERISTICS (For 100m of Cable)

Mutual Capacitance:	13.5 PF/FT at 1 MHz	
Dielectric Withstanding:	1500V RMS	
Impedance:	100 ± 15 Ω 1-100 MHz	
Impedance, Smoothed:	100 ± 10 Ω Typical 5 -100 MHz	
Return Loss:	$1 \leq f < 10 \text{ MHz}$ $10 \leq f < 20 \text{ MHz}$ $20 \leq f \leq 100 \text{ MHz}$	20 + 6 LOG(f) dB MIN* 26 dB MIN* 26 - 5LOG(f/20) dB MIN*
NEXT:	$1 \leq f \leq 100 \text{ MHz}$	35.3 -15 LOG(f/100) dB MIN
ACRF:	$1 \leq f \leq 100 \text{ MHz}$	23.8 - 20 LOG(f/100) dB MIN
Insertion Loss:	$1 \leq f \leq 100 \text{ MHz}$	1.5[1.967 SQRT(f) + 0.023(f) + 0.050/SQRT(f)] dB MAX
Delay:	$1 \leq f \leq 100 \text{ MHz}$	534 + 36/SQRT(F) ns MAX
Delay Skew:	$1 \leq f \leq 100 \text{ MHz}$	<25ns
ELTCTL:	$1 \leq f \leq 30 \text{ MHz}$	35-20 LOG(f)
Coupling Attenuation:	$30 \leq f \leq 100 \text{ MHz}$	≥ 60 dB E3* Per IEC 62153-4-9
Velocity of Propagation	68%	

* Per ODVA Volume 2 Ethernet/IP

Note: All testing is conducted off the reel

PERFORMANCE CHARACTERISTICS

Flex Life:	(126 cycles/minute @ 20°C)	1 million cycle test (10x Cable OD, minimum radius) 10 million cycle test (20x Cable OD, minimum radius)
Torsion Test:	(1lb load, 360°, 71 Cycles/min @ 20°C)	3 million cycle test



Southwire

**CABLETECH
SUPPORT™**

Services