

# MGG CABLES

Flexible High Temperature Cable, Temp Rating 450°C, 600V



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Flexible stranded 27% nickel plated, annealed copper
2. **Insulation:** Phlogopite mica tape with fiberglass braid jacket
3. **Braid:** Fiberglass braid jacket
4. **Cabling:** Conductors are cabled with a left hand lay
5. **Jacket:** Fiberglass braid jacket is treated with a high temperature saturant

## APPLICATIONS AND FEATURES:

Used in wiring equipment that will be exposed to high temperatures. Flexible.

Excellent flame resistance. Can withstand up to 2400°F short term. Also available in Power and Instrumentation Cables.

## SPECIFICATIONS:

- UL 1277 Vertical Cable Tray Flame Tests (70,000 BTU/Hr)
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- RoHS-3 Complies with European Directive 2015/863

**Table 1 – Weights and Measurements**

| Stock Number | Cond. Size<br>AWG/Kcmil | Cond. Number<br>No. | Approx. OD<br>inch | Approx. Weight<br>lb/1000ft | Temp. Rating<br>°C | Standard (UL or other)<br>Style/Type |
|--------------|-------------------------|---------------------|--------------------|-----------------------------|--------------------|--------------------------------------|
| C54340       | 14                      | 19                  | 0.760              | 450                         | 450                | UL                                   |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Weights and Measurements (Metric)**

| Stock Number | Cond. Size<br>AWG/Kcmil | Cond. Number<br>No. | Approx. OD<br>mm | Approx. Weight<br>kg/km | Temp. Rating<br>°C | Standard (UL or other)<br>Style/Type |
|--------------|-------------------------|---------------------|------------------|-------------------------|--------------------|--------------------------------------|
| C54340       | 14                      | 19                  | 19.30            | 670                     | 450                | UL                                   |

