MGG CABLES

Flexible High Temperature Cable, Temp Rating 450°C, 600V



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Flexible stranded 27% nickel plated, annealed copper
2. **Insulation:** Phlogopite mica tape with fiberglass braid jacket
3. **Braid:** Fiberglass braid jacket
4. **Cabling:** Conductors are cabled with a left hand lay
5. **Jacket:** Fiberglass braid jacket is treated with a high temperature saturant

APPLICATIONS AND FEATURES:

Used in wiring equipment that will be exposed to high temperatures. Flexible.

Excellent flame resistance. Can withstand up to 2400°F short term. Also available in Power and Instrumentation Cables.

SPECIFICATIONS:

- UL 1277 Vertical Cable Tray Flame Tests (70,000 BTU/Hr)
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- RoHS-3 Complies with European Directive 2015/863

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	inch	lb/1000ft	°C	Style/Type
C54220	16	7	0.420	129	450	UL

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	mm	kg/km	°C	Style/Type
C54220	16	7	10.67	192	450	UL