

# CU Compressed 35kV NLEPR Insulation 100% IL Black SIM-PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Copper, 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level, Tape Shield, SIMpull Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

## APPLICATIONS AND FEATURES:

Southwire's 35KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -25°C for cold bend and cold impact and marked with "LTDD" when CSA listed or dual UL/CSA listed. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.001

- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

### SAMPLE PRINT LEGEND:

{SQFTG\_DUAL} SOUTHWIRE SIMpull® POWER CABLE {UL} XXX KCMIL CU 345 MILS NL-EPR 35KV 100% INS LEVEL 25%TS MV-105 FOR CT USE SUN RES (NESC) -- {CSA} 500 KCMIL CU 8.76mm (345 mils) NL-EPR 35KV 100% INS LEVEL 25%TS SR TC-ER 105°C FT4 -25°C LTDD -- PAT www.patentSW.com -- RoHS

**Table 1 – Weights and Measurements**

| Stock Number | Cond. Size | Strand Count   | Diameter Over Conductor | Diameter Over Insulation | Diameter Over Insulation Shield | Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight | Max Pull Tension | Min Bending Radius | Conduit Size* |
|--------------|------------|----------------|-------------------------|--------------------------|---------------------------------|------------------|------------|---------------|----------------|------------------|--------------------|---------------|
|              | AWG/Kcmil  | No. of Strands | inch                    | inch                     | inch                            | mil              | inch       | lb/1000ft     | lb/1000ft      | lb               | inch               | inch          |
| 555839       | 1/0        | 19             | 0.361                   | 1.090                    | 1.150                           | 80               | 1.330      | 418           | 1073           | 844              | 15.9               | 4.0           |
| 555847       | 2/0        | 19             | 0.405                   | 1.134                    | 1.194                           | 80               | 1.374      | 506           | 1195           | 1064             | 16.4               | 4.0           |
| 555854       | 3/0        | 19             | 0.456                   | 1.184                    | 1.244                           | 80               | 1.424      | 617           | 1344           | 1342             | 17.0               | 4.0           |
| 555862       | 4/0        | 19             | 0.512                   | 1.240                    | 1.300                           | 80               | 1.480      | 756           | 1527           | 1692             | 17.7               | 4.5           |
| 555870       | 250        | 37             | 0.558                   | 1.294                    | 1.385                           | 80               | 1.565      | 881           | 1742           | 2000             | 18.7               | 4.5           |
| 551986       | 350        | 37             | 0.661                   | 1.397                    | 1.457                           | 80               | 1.637      | 1195          | 2090           | 2800             | 19.6               | 4.5           |
| 555888       | 500        | 37             | 0.789                   | 1.502                    | 1.562                           | 110              | 1.802      | 1666          | 2743           | 4000             | 21.6               | 5.0           |
| 957316       | 750        | 61             | 0.968                   | 1.714                    | 1.774                           | 110              | 2.014      | 2454          | 3714           | 6000             | 24.1               | 6.0           |
| 608992       | 1000       | 61             | 1.117                   | 1.863                    | 1.923                           | 110              | 2.163      | 3237          | 4623           | 8000             | 25.9               | 6.0           |
| 585498       | 1250       | 91             | 1.250                   | 2.000                    | 2.060                           | 110              | 2.300      | 4019          | 5524           | 10000            | 27.6               |               |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Conduit size based on 3 phase 40% fill-factor without ground

**Table 2 – Electrical and Engineering Data**

| Cond. Size | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Shield Short Circuit Current 6 Cycles | Allowable Ampacity In Duct 90/105°C | Allowable Ampacity In Air 90/105°C |
|------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|---------------------------------------|-------------------------------------|------------------------------------|
| AWG/Kcmil  | Ω/1000ft             | Ω/1000ft             | MΩ*1000ft                   | Ω/1000ft                   | Ω/1000ft                | Ω/1000ft                    | Amp                                   | Amp                                 | Amp                                |
| 1/0        | 0.102                | 0.128                | 0.057                       | 0.052                      | 0.479 + j0.309          | 0.129 + j0.052              | 3590                                  | 200/215                             | 260/290                            |
| 2/0        | 0.081                | 0.102                | 0.053                       | 0.050                      | 0.449 + j0.295          | 0.103 + j0.05               | 3727                                  | 230/245                             | 300/330                            |
| 3/0        | 0.064                | 0.081                | 0.049                       | 0.048                      | 0.423 + j0.281          | 0.082 + j0.048              | 3885                                  | 260/275                             | 345/380                            |
| 4/0        | 0.051                | 0.065                | 0.046                       | 0.046                      | 0.402 + j0.266          | 0.066 + j0.046              | 4058                                  | 295/315                             | 395/445                            |
| 250        | 0.043                | 0.056                | 0.043                       | 0.045                      | 0.387 + j0.253          | 0.057 + j0.045              | 4226                                  | 325/345                             | 440/490                            |
| 350        | 0.031                | 0.041                | 0.039                       | 0.043                      | 0.362 + j0.23           | 0.042 + j0.043              | 4545                                  | 390/415                             | 545/605                            |
| 500        | 0.022                | 0.030                | 0.034                       | 0.041                      | 0.338 + j0.206          | 0.031 + j0.041              | 4941                                  | 465/500                             | 680/755                            |
| 750        | 0.014                | 0.023                | 0.029                       | 0.039                      | 0.313 + j0.177          | 0.024 + j0.038              | 5527                                  | 565/610                             | 870/970                            |
| 1000       | 0.011                | 0.019                | 0.026                       | 0.037                      | 0.296 + j0.158          | 0.02 + j0.037               | 5989                                  | 640/690                             | 1040/1160                          |
| 1250       | 0.009                | 0.018                | 0.024                       | 0.036                      | 0.283 - j0.112          | 0.019 - j0.22               | 6413                                  | 715/770                             | 1185/1320                          |

\* Ampacities are based on:

\* For Duct: Table 310.60(C)(77) Detail 1.

\* For Free Air: Table 310.60(C)(69).



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



**Southwire**

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.001

- \* Inductive impedance is based on non-ferrous conduit with one diameter spacing.
- \* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
- \* Capacitive Reactance is between Phase-to-Shield.

