

## 22AWG 4 Pair Shielded Industrial Ethernet Cable

Cat 5e. PLTC. ITC.AWM Style 2463. 75°C. Sunlight Resistance. Oil Resistant I & II. RoHS-2




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** 22AWG, stranded, tinned copper per ASTM B33 and B174
2. **Insulation:** High Density Polyethylene (HDPE)
3. **Pairs:** Color coded singles twisted into pairs
4. **Color Code:** 1PR - White/Blue, Blue; 2PR - White/Orange, Orange; 3PR - White/Green, Green; 4PR - White/Brown, Brown
5. **Assembly:** Twisted pairs cabled together with filler and wrapped with clear polyester tape to form a round cable
6. **Shielding:** An overall shield of 38 AWG tinned copper braid (75% coverage) is applied over the cable core and under a second aluminized polyester foil shield (100% coverage).
7. **Jacket:** Teal, Thermoplastic Elastomer (TPE)

### APPLICATIONS AND FEATURES:

Shielded Ethernet Cat 5e cable designed for the harsh industrial environment and provides excellent protection against EMI interference. It is suitable for continuous flexing cable track and torsion applications. For use for wiring network interconnections. Industrial strength jacket provides excellent resistance to low temperatures (-40°C), common oils and chemicals, flame, UV and weather exposure. For use in Class I Division 2 applications in accordance with NEC® Article 501.10(B)(3).

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 13 Power-Limited Circuit Cables
- UL 758 Standard for Appliance Wiring Material Style 2463 (80C, 600V)
- UL 2250 Instrumentation Tray Cable
- CSA C22.2 No.214 Communications cables
- RoHS-2 (European Directive 2011/65/EU)
- CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive



Southwire

**CABLETECH  
SUPPORT™**

Services

**SAMPLE PRINT LEGEND:**

Southwire Industrial Ethernet Cat 5e Flexing 4 PR 22AWG SF/UTP EXXXXXX-- (UL) TYPE PLTC Oil Res I & II SUN RES OR ITC 75C OR C(UL)US TYPE CMX OUTDOOR - CM 75C OR AWM 2463 80C 600V -- RoHS-2 CE-- (Lot Designator) (Sequential Footage) Made in USA



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



**Southwire**

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Number of Pairs	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	Max Plug to Plug Transmission Distance + POE
	AWG/Kcmil	pair	strand	mil	mil	inch	lb/1000ft	$\Omega$ /1000ft	meter
648564	22	4	19	13	41	0.345	58.4	6	100

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**ELECTRICAL CHARACTERISTICS (For 100m of Cable)**

Mutual Capacitance:	13.5 PF/FT at 1 MHz	
Dielectric Withstanding:	2000V RMS	
Impedance:	100 $\pm$ 15 $\Omega$ 1-100 MHz	
Return Loss:	$1 \leq f < 10$ MHz $10 \leq f < 20$ MHz $20 \leq f \leq 100$ MHz	20 + 6 LOG(f) dB MIN* 26 dB MIN* 26 - 5LOG(f/20) dB MIN*
NEXT:	$1 \leq f \leq 100$ MHz	35.3 - 15 LOG(f/100) dB MIN
PSNEXT:	$1 \leq f \leq 100$ MHz	32.3 - 15 LOG(f/100) dB MIN
ACRF:	$1 \leq f \leq 100$ MHz	23.8 - 20 LOG(f/100) dB MIN
PSACRF:	$1 \leq f \leq 100$ MHz	20.8 - 20 LOG(f/100) dB MIN
Insertion Loss:	$1 \leq f \leq 100$ MHz	1.02[1.967 SQRT(f) + 0.023(f) + 0.050/SQRT(f)] dB MAX
Delay:	$1 \leq f \leq 100$ MHz	534 + 36/SQRT(F) ns MAX
Delay Skew:	$1 \leq f \leq 100$ MHz	<20ns PER IEC 61156-5
Coupling Attenuation:	$30 \leq f \leq 100$ MHz	$\geq 60$ dB E3* Per IEC 62153-4-9
Velocity of Propagation	69%	

\* Per ODVA Volume 2 Ethernet/IP

Note: All testing is conducted off the reel

**PERFORMANCE CHARACTERISTICS**

Flex Life:	(126 cycles/minute @ 20°C)	1 million cycle test (10x Cable OD, minimum radius) 10 million cycle test (20x Cable OD, minimum radius)
Torsion Test:	(1lb load, 360°, 71 Cycles/min @ 20°C)	3 million cycle test



**Southwire**



Services