

15kV CU 100% EPR (EAM) Full Neutral LLDPE

Single Conductor, 175 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 100% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer. A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 175 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

For information about our Cable-Rejuvenation Services please visit us at: [Cable-Rejuvenation Services](#)

You can email us at: [Cable-Rejuvenation Services](#)

APPLICATIONS AND FEATURES:

Southwire's 15kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request



SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 15000 VOLTS EPR INSULATION 175 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	2 (Solid)	0.257	0.645	175	0.735	16x14	0.164	50	0.963	701	7.7	530
TBA	1 (Solid)	0.289	0.677	175	0.767	20x14	0.131	50	0.995	825	8.0	669
TBA	1 (19)	0.322	0.710	175	0.800	20x14	0.131	50	1.028	841	8.2	669
TBA	1/0 (Solid)	0.324	0.712	175	0.802	25x14	0.105	50	1.030	975	8.2	844
TBA	3/0 (19)	0.456	0.844	175	0.934	25x12	0.066	50	1.196	1420	9.6	1342
TBA	250 (37)	0.558	0.954	175	1.044	25x10	0.041	50	1.348	2046	10.8	2000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω /1000ft	Ω /1000ft	M Ω *1000ft	Ω /1000ft	A/1000ft	W/1000ft	Ω /1000ft	Ω /1000ft	Amp	Amp	Amp
2 (Solid)	0.162	0.204	0.047	0.052	0.104	3.42	0.258 + j0.772	0.204 + j0.051	5579	155	195
1 (Solid)	0.128	0.162	0.044	0.050	0.112	3.69	0.216 + j0.767	0.162 + j0.048	6974	175	220
1 (19)	0.128	0.162	0.041	0.048	0.121	3.98	0.216 + j0.765	0.162 + j0.049	6974	175	220
1/0 (Solid)	0.102	0.128	0.040	0.048	0.122	4.02	0.182 + j0.762	0.128 + j0.046	8718	200	250
3/0 (19)	0.064	0.081	0.032	0.044	0.155	5.10	0.135 + j0.750	0.081 + j0.044	13852	260	315
250 (37)	0.043	0.056	0.027	0.042	0.178	5.86	0.111 + j0.740	0.056 + j0.042	22019	318	360

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



Southwire

**CABLETECH
SUPPORT™**

Services

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	2 (Solid)	6.53	16.38	4.44	18.67	16x14	0.54	1.27	24.46	1043	195.58	2359
TBA	1 (Solid)	7.34	17.20	4.44	19.48	20x14	0.43	1.27	25.27	1228	203.20	2977
TBA	1 (19)	8.18	18.03	4.44	20.32	20x14	0.43	1.27	26.11	1252	208.28	2977
TBA	1/0 (Solid)	8.23	18.08	4.44	20.37	25x14	0.34	1.27	26.16	1451	208.28	3756
TBA	3/0 (19)	11.58	21.44	4.44	23.72	25x12	0.22	1.27	30.38	2113	243.84	5972
TBA	250 (37)	14.17	24.23	4.44	26.52	25x10	0.13	1.27	34.24	3045	274.32	8900

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (Solid)	0.5315	0.67	0.0143	0.1706	0.341	11.2205	$0.258 + j0.772$	$0.204 + j0.051$	5579	155	195
1 (Solid)	0.4199	0.53	0.0134	0.1640	0.367	12.1063	$0.216 + j0.767$	$0.162 + j0.048$	6974	175	220
1 (19)	0.4199	0.53	0.0125	0.1575	0.397	13.0577	$0.216 + j0.765$	$0.162 + j0.049$	6974	175	220
1/0 (Solid)	0.3346	0.42	0.0122	0.1575	0.400	13.1890	$0.182 + j0.762$	$0.128 + j0.046$	8718	200	250
3/0 (19)	0.2100	0.27	0.0098	0.1444	0.509	16.7323	$0.135 + j0.750$	$0.081 + j0.044$	13852	260	315
250 (37)	0.1411	0.18	0.0082	0.1378	0.584	19.2257	$0.111 + j0.740$	$0.056 + j0.042$	22019	318	360

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN
Calculator



Southwire

**CABLETECH
SUPPORT™**

Services