

PTFE Insulation & Jacket

500°F 260°C Continuous, 600°F 316°C Single Reading



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Thermocouple wire per ANSI MC 96.1 & ASTM E230 (Solid or stranded available)
2. **Insulation:** Fused PTFE Tape
3. **Overall Jacket:** Fused PTFE Tape

APPLICATIONS AND FEATURES:

Widely used in petrochemical facilities, the aerospace industry and also in temperature sensors. Also provides stability in low temperature applications. Excellent flame retardance and chemical resistance. Excellent resistance to acids, solvents and moisture. Excellent resistance to abrasion.

Stainless Steel, Inconel metal, or Tin Plated Copper overbraid is available on request. Type E, J, K, T and other Types available on request.

SPECIFICATIONS:

- ASTM E230 Temperature-Electromotive Force (emf) Tables for Standardized Thermocouples
- ANSI MC 96.1 Temperature Measurement Thermocouples



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	mil	mil	inch	lb/1000ft	°C	Style/Type
C4T_00	24	2	6	6	0.080 x 0.130	4	260 / 316	Type E, J, K, T
C4T_10	22	2	6	6	0.085 x 0.141	6	260 / 316	Type E, J, K, T
C4T_20	20	2	6	6	0.092 x 0.154	9	260 / 316	Type E, J, K, T
C4T_30	18	2	6	6	0.100 x 0.170	14	260 / 316	Type E, J, K, T
C4T_40	16	2	6	6	0.111 x 0.192	20	260 / 316	Type E, J, K, T
C4T_05	24(7)	2	6	6	0.084 x 0.138	4	260 / 316	Type E, J, K, T
C4T_25	20(7)	2	6	6	0.096 x 0.162	9	260 / 316	Type E, J, K, T
C4T_45	16(7)	2	6	6	0.119 x 0.208	20	260 / 316	Type E, J, K, T

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

0=Type E // 1=Type J // 2=Type K // 3=Type T

Conductor insulation and overall jacket are color coded per ANSI MC 96.1 and ASTM E230.

International color codes available on request.

Available in standard and special limits of error per ANSI MC 96.1, ASTM E230 and IEC 584.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	mm	mm	mm	kg/km	°C	Style/Type
C4T_00	24	2	0.15	0.15	2.03 x 3.30	6	260 / 316	Type E, J, K, T
C4T_10	22	2	0.15	0.15	2.16 x 3.58	9	260 / 316	Type E, J, K, T
C4T_20	20	2	0.15	0.15	2.34 x 3.91	13	260 / 316	Type E, J, K, T
C4T_30	18	2	0.15	0.15	2.54 x 4.32	21	260 / 316	Type E, J, K, T
C4T_40	16	2	0.15	0.15	2.82 x 4.88	30	260 / 316	Type E, J, K, T
C4T_05	24(7)	2	0.15	0.15	2.13 x 3.51	6	260 / 316	Type E, J, K, T
C4T_25	20(7)	2	0.15	0.15	2.44 x 4.11	13	260 / 316	Type E, J, K, T
C4T_45	16(7)	2	0.15	0.15	3.02 x 5.28	30	260 / 316	Type E, J, K, T

