

Southwire® Machine Flex® Hookup PVC

105°C Dry. 60/75°C Moisture Resistant. 600/1000 Volts. Flexible Stranded Tinned Copper Conductor. PVC Insulation .



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Flexible stranded tinned copper per ASTM B33, ASTM B172, ASTM B173
 2. **Insulation:** Polyvinyl Chloride (PVC)
- Colors: Other Colors available; including Green with 2x15% +/- 5% Tolerance Yellow Extruded Stripe. Other stripes available.
 - Extruded stripes limited to sizes 4/0 AWG and smaller. 250 kcmil available in solid colors only.

APPLICATIONS AND FEATURES:

Southwire's Machine Flex® power cables are suited for use in wet and dry areas, conduits, ducts, troughs, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 75°C for normal operation in wet and dry locations, 90°C for emergency overload, and 150°C for short circuit conditions. 1/0 AWG & larger rated for CT use.

SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ASTM B173 Rope-Lay-Stranded Copper Conductors Having Concentric-Stranded Members
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 758 Standard for Appliance Wiring Material
- UL 1063 Machine Tool Wiring (MTW)
- CSA C22.2 No. 127 Equipment and Lead Wires
- CSA C22.2 No. 210 Appliance Wiring Material Products
- CT USE - As Type THHW in 1 /0 AWG & Larger
- Oil Res I & Sun Res - AWG 8 & Larger
- AWM 1032; AWG 18-6 AWM 1011/1015/1230/1335; AWG 18-10
AWM 1011/1028/1231/1344; AWG 8 AWM 1232/1283/1346/10269; AWG 6-2
AWM 1232/1284/1338/10269; AWG 1- 4/0 AWM 1284/1339/10269; Kcmil 250
- CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Feb. 9, 2024, 11:25 a.m. UTC REVISION: 1.000.007

SAMPLE PRINT LEGEND:

- SOUTHWIRE 18 AWG (0.823mm²) E51583 (PLANT ID CODE) (UL) MTW OR AWM 1011/1015/1230/1335/1345 600V OR 1032 1000V MOISTURE RESISTANT VW-1 -- 156205 CSA TEW 105°C 600V FT1 OR AWM I A/B 105°C 600V FT1 -- CE RoHS-2 MADE IN USA
- SOUTHWIRE® 8 AWG (8.37mm²) E69567 (PLANT ID CODE) (UL) BC-5W2 OR MTW OR THHW OR AWM 1011/1028/1231/1337 600V OR 1032 1000V MOISTURE RESISTANT OIL RES I SUN RES VW-1 -- 156205 CSA TEW 105°C 600V FT1 OR AWM I A/B 105°C 600V FT1-CE RoHS-2 MADE IN USA
- SOUTHWIRE® 250 MCM (127mm²) E51583 (PLANT ID CODE) (UL) MTW OR THHW FOR CT USE OR AWM 1284/1339 600V OR 10269 1000V. OIL RES 1 SUN RES VW-1 - 156205 CSA AWM A/B 105°C 600 V - CE RoHS-2 MADE IN USA

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Insul. Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil	No. of Strands	inch	mil	inch	lb/1000ft	lb/1000ft
TBA	20	10	0.036	30	0.099	3	7.09
TBA	18	16	0.044	30	0.106	5	9
F16502122C2	16	26	0.059	30	0.117	8	13
F14647122C2	14	41	0.073	30	0.132	13	18
F12276122C2	12	65	0.094	30	0.151	20	27
F10237072C2	10	105	0.117	30	0.175	32	41
TBA	8	133	0.153	45	0.252	51	72
F0618907C2	6	133	0.198	60	0.324	81	113
F0412707C2	4	133	0.235	60	0.387	129	166
F0213312C2	2	133	0.290	60	0.420	210	259
TBA	1	259	0.345	80	0.521	258	324
F1T09704C2	1/0	259	0.390	80	0.561	326	401
F2T1000400	2/0	259	0.409	80	0.585	426	513
F3T10304C2	3/0	259	0.533	80	0.666	518	601
F4T1050400	4/0	551	0.550	80	0.740	665	785
TBA	250	2451	0.682	95	0.835	772	934

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item



Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Amp	Amp
TBA	20	0.4	8	11.319	14.725	-	-
TBA	18	0.4	13	7.148	8.613	-	14
F16502122C2	16	0.4	21	4.487	5.406	-	18
F14647122C2	14	0.5	33	2.814	3.391	20	25
F12276122C2	12	0.6	52	1.774	2.137	25	30
F10237072C2	10	0.7	83	1.111	1.339	35	40
TBA	8	1	132	0.715	0.861	50	55
F0618907C2	6	1.2	209	0.450	0.541	65	75
F0412707C2	4	1.5	333	0.282	0.340	85	95
F0213312C2	2	1.8	530	0.179	0.216	115	130
TBA	1	2	669	0.143	0.172	130	145
F1T09704C2	1/0	2.2	844	0.113	0.136	150	170
F2T1000400	2/0	2.6	1064	0.090	0.108	175	195
F3T10304C2	3/0	2.6	1342	0.072	0.087	200	225
F4T1050400	4/0	2.9	1692	0.057	0.069	230	260
TBA	250	3.3	2000	0.048	0.059	255	290

† Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

† Ampacities have been adjusted for more than Three Current-Carrying Conductors.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

