

CU 600V PE PVC Cable Color Method 1 Table 1 Traffic Signal IMSA 19-1

Multi-conductor nonshielded 600V Polyethylene Insulation, Polyvinyl Chloride (PVC) Jacket



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid or stranded annealed bare copper class B per ASTM B3 and B8
2. **Insulation:** Polyethylene PE
3. **Rip Chord:** High strength rip chord for ease of jacket removal
4. **Separator:** Polyester tape
5. **Jacket:** Black polyvinyl chloride PVC jacket

APPLICATIONS AND FEATURES:

Southwire's IMSA 19-1 cable meets the requirements of International Municipal Signal Association IMSA 19-1 specification. Rated for use in traffic signal, traffic control systems, underground conduit and aerial use where supported by a messenger. IMSA 19-1 600 Volt series cables run from the traffic light to the controller station. The conductors are bare annealed copper solid or stranded class B and covered with an abrasion, sunlight and moisture resistant polyvinyl chloride jacket. The insulated conductors are twisted and wrapped with a polyester tape. A ripcord is added under the black polyvinyl chloride jacket for ease of removal. These cables are capable of operating continuously at a conductor temperature between -20°C and 75°C.

- Cable is manufactured by Southwire Company in their Waukegan, IL plant USA.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- EPA 40 CFR, Part 26, Subpart C heavy metals per Table 1, TCLP method
- IMSA 19-1

SAMPLE PRINT LEGEND:

SOUTHWIRE® YEAR SIZE 600V IMSA 19-1 CABLE SEQUENTIAL FOOT MARK.



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	Min Bending Radius
	AWG	No.	strands	inch	mil	mil	inch	lb /1000ft	Ω /1000ft	inch
14 AWG										
593124	14	2	1	0.064	25	45	0.318	62	2.570	1.3
593125	14	3	1	0.064	25	45	0.335	74	2.570	1.3
579047	14	4	1	0.064	25	45	0.365	93	2.570	1.5
593126	14	5	1	0.064	25	45	0.398	114	2.570	1.6
593127	14	7	1	0.064	25	45	0.432	146	2.570	1.7
581384	14	2	7	0.070	25	45	0.336	67	2.630	1.3
578924	14	3	7	0.070	25	45	0.354	79	2.630	1.4
581396	14	4	7	0.070	25	45	0.386	99	2.630	1.5
578889	14	5	7	0.070	25	45	0.422	122	2.630	1.7
578890	14	7	7	0.070	25	45	0.459	156	2.630	1.8
581399	14	9	7	0.070	25	60	0.565	216	2.630	2.3
578928	14	16	7	0.070	25	60	0.698	350	2.630	2.8
578892	14	21	7	0.070	25	60	0.773	455	2.630	3.1

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

† Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

† Ampacities have been adjusted for more than Three Current-Carrying Conductors.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

