

CU 600V NLEPR PE TRANSIT VITAL SIGNAL CABLE

600 Volt 90°C AREMA PART 10.3.16. Aerial / Tunnel Installations for Transit Systems



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid Uncoated Copper
2. **Insulation:** High Performance No Lead Ethylene Propylene Rubber NL-EPR
3. **Fillers:** Non-Wicking Flame Retardant Fillers with 8 mil Cushioning Tape
4. **Rip Chord:** Rip Chord for Ease of Jacket Removal
5. **Jacket:** Polyethylene PE Jacket

APPLICATIONS AND FEATURES:

Southwire 600V ECO Friendly No Lead EPR/PE Vital Signal Cable is suited for use in vital transit circuit safety systems where reduced sag, low conductor fatigue, and secure service life are a concern. May be installed in wet or dry locations. These cables are capable of operating continuously at a conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload conditions, and 250°C for short circuit conditions.

- Mechanically Rugged
- High Performance No Lead EPR
- Excellent Moisture Resistance
- Resistant to Heat Aging and Environmental Hazards
- Cleanly Strips from Conductor
- Superior Deformation Resistance
- 40 Year Life
- RoHS/Proposition 65 Compliant
- Conductors Number Coded with One in Each layer Marked as "Tracer" for Quick Identification.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B496 Compact Round Concentric-lay-standard copper
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- AREMA Signal Manual Part 10.3.19 for EPR Type I Insulation
- AREMA Signal Manual Part 10.3.21 for PE Type II Jacket



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

Table 1 – Physical and Electrical Data

Cond. Size AWG/kcmil	Strand Count No. of Strands	Cond. Number No.	Cond. Shape	Insul. Thickness mil	Jacket Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
14	1	3	TRANSIT VITAL SIGNAL CABLE	60	60	0.550	151
14	1	5	TRANSIT VITAL SIGNAL CABLE	60	80	0.689	251
14	1	7	TRANSIT VITAL SIGNAL CABLE	60	80	0.744	303
14	1	12	TRANSIT VITAL SIGNAL CABLE	60	95	0.987	497
9	1	3	TRANSIT VITAL SIGNAL CABLE	60	80	0.698	311
9	1	5	TRANSIT VITAL SIGNAL CABLE	60	80	0.825	432
9	1	7	TRANSIT VITAL SIGNAL CABLE	60	95	0.925	590
9	1	12	TRANSIT VITAL SIGNAL CABLE	60	95	1.197	943

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

