

35kV CU 100% EPR (EAM) Full Neutral LLDPE

Single Conductor, 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 100% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 35kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 35000 VOLTS EPR INSULATION 345 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Southwire

**CABLETECH
SUPPORT™**

Services

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	1/0 (Solid)	0.324	1.052	345	1.162	25x14	0.105	50	1.390	1300	11.1	844
622149	1/0 (19)	0.361	1.082	345	1.192	16x12	0.103	50	1.453	1381	11.6	844
627998	2/0 (19)	0.405	1.126	345	1.236	13x10	0.080	50	1.539	1634	12.3	1064
TBA	3/0 (19)	0.456	1.184	345	1.294	25x12	0.066	50	1.556	1782	12.4	1342
628021	4/0 (19)	0.512	1.232	345	1.342	20x10	0.052	50	1.645	2185	13.2	1692
TBA	250 (37)	0.558	1.294	345	1.404	25x10	0.041	75	1.758	2526	14.1	2000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω /1000ft	Ω /1000ft	M Ω *1000ft	Ω /1000ft	A/1000ft	W/1000ft	Ω /1000ft	Ω /1000ft	Amp	Amp	Amp
1/0 (Solid)	0.102	0.128	0.061	0.055	0.190	14.6	0.182 + j0.749	0.128 + j0.053	8718	205	245
1/0 (19)	0.102	0.128	0.057	0.054	0.203	15.6	0.182 + j0.746	0.128 + j0.054	8865	205	245
2/0 (19)	0.081	0.102	0.053	0.053	0.217	16.7	0.156 + j0.741	0.102 + j0.053	11450	235	280
3/0 (19)	0.064	0.081	0.049	0.050	0.234	18.0	0.135 + j0.738	0.081 + j0.050	13852	265	315
4/0 (19)	0.051	0.065	0.046	0.049	0.253	19.4	0.119 + j0.731	0.065 + j0.050	17615	305	350
250 (37)	0.043	0.056	0.043	0.048	0.266	20.4	0.110 + j0.728	0.056 + j0.048	22019	321	

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	1/0 (Solid)	8.23	26.72	8.76	29.51	25x14	0.34	1.27	35.31	1935	281.94	3756
622149	1/0 (19)	9.17	27.48	8.76	30.28	16x12	0.34	1.27	36.91	2055	294.64	3756
627998	2/0 (19)	10.29	28.60	8.76	31.39	13x10	0.26	1.27	39.09	2432	312.42	4735
TBA	3/0 (19)	11.58	30.07	8.76	32.87	25x12	0.22	1.27	39.52	2652	314.96	5972
628021	4/0 (19)	13.00	31.29	8.76	34.09	20x10	0.17	1.27	41.78	3252	335.28	7529
TBA	250 (37)	14.17	32.87	8.76	35.66	25x10	0.13	1.91	44.65	3759	358.14	8900

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0 (Solid)	0.3346	0.42	0.0186	0.1804	0.623	47.9003	$0.182 + j0.749$	$0.128 + j0.053$	8718	205	245
1/0 (19)	0.3346	0.42	0.0174	0.1772	0.666	51.1811	$0.182 + j0.746$	$0.128 + j0.054$	8865	205	245
2/0 (19)	0.2657	0.33	0.0162	0.1739	0.712	54.7900	$0.156 + j0.741$	$0.102 + j0.053$	11450	235	280
3/0 (19)	0.2100	0.27	0.0149	0.1640	0.768	59.0551	$0.135 + j0.738$	$0.081 + j0.050$	13852	265	315
4/0 (19)	0.1673	0.21	0.0140	0.1608	0.830	63.6483	$0.119 + j0.731$	$0.065 + j0.050$	17615	305	350
250 (37)	0.1411	0.18	0.0131	0.1575	0.873	66.9291	$0.110 + j0.728$	$0.056 + j0.048$	22019	321	

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

CN
Calculator



Southwire

**CABLETECH
SUPPORT™**

Services