

# Quadruplex LLDPE Service Drop. ACSR Neutral - Messenger

Aluminum Conductors With Linear Low Density Polyethylene Insulation.




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Conductors are stranded, compressed 1350-H19 aluminum
2. **Messenger:** ACSR Neutral
3. **Insulation:** Linear Low Density Polyethylene (LLDPE)

## APPLICATIONS AND FEATURES:

Used to supply power, usually from a pole-mounted transformer, to the user's service head where connection to the service entrance cable is made. To be used at voltages of 600 volts phase-to-phase or less and at conductor temperatures 75°C for Linear Low Density Polyethylene (LLDPE) insulated conductors.

## SPECIFICATIONS:

- ASTM B230 Aluminum, 1350-H19 Wire for Electrical Purposes
- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B400 Standard Specification for Compact Round Concentric-Lay-Stranded, Aluminum 1350 Conductors
- ASTM B901 Standard Specification for Compressed Round Stranded Aluminum Conductors Using Single Input Wire Construction. (The number of strands for both phase and neutral may differ)
- ICEA S-76-474 Standard for Neutral-Supported Power Cable Assemblies with Weather-Resistant Extruded Insulation Rated 600V



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



**Southwire**

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

**Table 1 – Weights and Measurements**

| Stock Number | Code Word | Phase Cond. Size | Phase Strand | Dia. Over Phase Conductor | Phase Insul. Thickness | Dia. Over Phase Insulation | Neutral Cond. Size | Approx. OD | Approx. Weight |
|--------------|-----------|------------------|--------------|---------------------------|------------------------|----------------------------|--------------------|------------|----------------|
|              |           | AWG/Kcmil        | No.          | inch                      | mil                    | inch                       | AWG/Kcmil          | inch       | lb/1000ft      |
| TBA          | Morochuca | 6                | 1            | 0.162                     | 45                     | 0.252                      | 6                  | 0.608      | 145            |
| 103176       | Chola     | 6                | 7            | 0.178                     | 45                     | 0.268                      | 6                  | 0.647      | 153            |
| TBA          | Morgan    | 4                | 1            | 0.204                     | 45                     | 0.294                      | 4                  | 0.71       | 217            |
| TBA          | Hackney   | 4                | 7            | 0.225                     | 45                     | 0.315                      | 4                  | 0.76       | 229            |
| 554112       | Palomino  | 2                | 7            | 0.283                     | 45                     | 0.373                      | 2                  | 0.9        | 347            |
| 103200       | Palomino  | 2                | 7            | 0.283                     | 45                     | 0.373                      | 2                  | 0.901      | 343            |
| TBA          | Costena   | 1/0              | 9            | 0.352                     | 60                     | 0.472                      | 1/0                | 1.139      | 549            |
| TBA          | Grullo    | 2/0              | 11           | 0.395                     | 60                     | 0.515                      | 2/0                | 1.243      | 677            |
| 103242       | Suffolk   | 3/0              | 17           | 0.443                     | 60                     | 0.563                      | 3/0                | 1.359      | 833            |
| TBA          | Suffolk   | 3/0              | 17           | 0.443                     | 60                     | 0.563                      | 3/0                | 1.359      | 837            |
| TBA          | Appaloosa | 4/0              | 18           | 0.498                     | 60                     | 0.618                      | 4/0                | 1.492      | 1038           |
| TBA          | Bronco    | 336.4            | 19           | 0.645                     | 60                     | 0.805                      | 336.4              | 1.943      | 1569           |
| TBA          | Gelding   | 336.4            | 19           | 0.645                     | 60                     | 0.805                      | 4/0                | 1.943      | 1494           |

All dimensions are nominal and subject to normal manufacturing tolerances

1. The actual number of strands may differ for single input wire per ASTM B901

**Table 2 – Electrical and Engineering Data**

| Code Word | Phase Cond. Size | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance @ 60Hz | GMR    | Allowable Ampacity In Air 90°C |
|-----------|------------------|----------------------|----------------------|----------------------------|--------|--------------------------------|
|           | AWG/Kcmil        | Ω/1000ft             | Ω/1000ft             | Ω/1000ft                   | ft     | Amp                            |
| Morochuca | 6                | 0.6523               | 0.8363               | 0.0357                     | 0.0053 | 60                             |
| Chola     | 6                | 0.6653               | 0.853                | 0.0365                     | 0.0054 | 60                             |
| Morgan    | 4                | 0.41                 | 0.5258               | 0.034                      | 0.0066 | 80                             |
| Hackney   | 4                | 0.4183               | 0.5363               | 0.0349                     | 0.0068 | 80                             |
| Palomino  | 2                | 0.2631               | 0.3373               | 0.0336                     | 0.0086 | 105                            |
| Palomino  | 2                | 0.2631               | 0.3373               | 0.0336                     | 0.0086 | 105                            |
| Costena   | 1/0              | 0.1653               | 0.212                | 0.0338                     | 0.0107 | 140                            |
| Grullo    | 2/0              | 0.1312               | 0.1682               | 0.0331                     | 0.0121 | 160                            |
| Suffolk   | 3/0              | 0.104                | 0.1335               | 0.032                      | 0.0139 | 185                            |
| Suffolk   | 3/0              | 0.104                | 0.1335               | 0.032                      | 0.0139 | 185                            |
| Appaloosa | 4/0              | 0.0825               | 0.1059               | 0.0314                     | 0.0157 | 210                            |
| Bronco    | 336.4            | 0.0519               | 0.0667               | 0.0314                     | 0.0204 | 280                            |
| Gelding   | 336.4            | 0.0519               | 0.0667               | 0.0311                     | 0.0204 | 280                            |

Notes:

1. DC resistances include a 1% length factor for plexing.
2. Inductive reactance assumes the neutral is carrying current.
3. Phase conductors assumed to be reverse lay stranded, compressed construction.
4. Phase spacing assumes cables are touching.
5. Resistances shown are for the phase conductor only.
6. Ampacity based on conductor temperature of 75°; ambient temperature of 40°C; emissivity 0.9; 2 ft./sec. wind in sun.



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



**Southwire**

**CABLETECH  
SUPPORT™**

Services

UPDATED: Dec. 11, 2023, 9:29 p.m. UTC REVISION: 1.000.000

| Size  | Code Word | OD (inches) |
|-------|-----------|-------------|
| #6    | Turkey    | 0.198       |
| #4    | Swan      | 0.250       |
| #2    | Sparrow   | 0.316       |
| 1/0   | Raven     | 0.398       |
| 2/0   | Quail     | 0.447       |
| 3/0   | Pigeon    | 0.502       |
| 4/0   | Penguin   | 0.684       |
| 336.4 | Merlin    | 0.563       |

