

Multi-Conductor CU 600 V FR-XLPE LCT Shielded CPE Jacket Control Cable Color Method 1 Table 2

Control Cable 600 Volt Copper Conductors, Flame Retardant Cross Linked Polyethylene (FR-XLPE) Insulation Shielded Chlorinated Polyethylene (CPE) Jacket, Control Cable Conductor Identification Method 1 Table 2. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 7 strands class B compressed bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Flame Retardant Cross Linked Polyethylene (FR-XLPE), 30 Mils thick for all cable sizes
3. **Filler:** Polypropylene filler on cables with 5 or less conductors
4. **Binder:** Polyester flat thread binder tape applied for cables with more than 5 conductors
5. **LCT Shielding:** 5 mils tape shield
6. **Rip Chord:** Rip chord for ease of jacket removal
7. **Overall Jacket:** Chlorinated Polyethylene (CPE)

APPLICATIONS AND FEATURES:

Southwire's 600 Volt control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. UL rated constructions can be used in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. UL rated constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10.

SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 1 Table 2
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Vertical Tray Flame Test (70,000 Btu/hr) and ICEA T-29-520 - (210,000 Btu/hr)
- VW-1 (Vertical-Wire) Flame Test



SAMPLE PRINT LEGEND:

UL Listed

SOUTHWIRE {UL} E75755 XX AWG CU X/C FR-XLPE E2 CDRS SHIELDED TYPE TC CPE JACKET 600V YEAR {SEQUENTIAL FOOTAGE MARKS} SEQ FEET

Non UL Listed

SOUTHWIRE XX AWG CU X/C FR-XLPE E2 CDRS SHIELDED CPE JACKET 600V SUN RES DIR BUR YEAR {SEQUENTIAL FOOTAGE MARKS} SEQ FEET

Table 1 – Physical and Electrical Data

Cond. Size	Cond. Number	Diameter Over Cond.	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance	AC Resistance @ 90°C	Min Bending Radius	Allowable Ampacity At 60°C *	Allowable Ampacity 75°C *	Allowable Ampacity 90°C *
AWG	No.	inch	mil	mil	inch	lb /1000ft	lb /1000ft	Ω /1000ft	Ω /1000ft	inch	Amp	Amp	Amp
10 AWG													
10	37	0.111	30	80	1.355	1198	1755	1.040	1.300	16.3	12	14	16

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on Table 310.15 (B)(16) of the NEC, 2017 Edition. Ampacities of insulated conductors rated up to and including 2000 Volts, based on ambient temperature of 30°C (86°F)

^ UL Listed part number

