

## CU 600 V FR-XLPE Shielded Thermoplastic CPE-TP Jacket Power Cable Color Method 1 Table 2

Power Cable 600 or 1000 Volt Three Conductor Copper, Fire Retardant Cross-Linked Polyethylene (FR-XLPE) insulation Shielded Thermoplastic Chlorinated Polyethylene (CPE-TP) Jacket Conductor Identification Method 1 Table 2



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Fire Retardant Cross Linked Polyethylene (FR-XLPE)
3. **Filler:** Paper or Polypropylene filler
4. **Binder:** Polyester flat thread binder tape
5. **Shield:** 5 mils tape shield
6. **Rip Cord:** Rip cord for ease of jacket removal
7. **Overall Jacket:** Thermoplastic Chlorinated Polyethylene (CPE-TP) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 600 Volt control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions.

### SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy

### SAMPLE PRINT LEGEND:

SOUTHWIRE MASTER-DESIGN XX AWG XX/C FR-XLPE CDRS 90C COPPER SHIELDED CPE JKT 600V SUN. RES. DIRECT BURIAL YEAR {SEQUENTIAL FOOTAGE MARKS} SEQ FEET



**Table 1 – Physical and Electrical Data**

Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Diameter Over Insulation	Jacket Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 90°C	Min Bending Radius	Allowable Ampacity At 60°C *	Allowable Ampacity 75°C *	Allowable Ampacity 90°C *
AWG	No.	strands	inch	mil	inch	mil	inch	lb /1000ft	Ω /1000ft	Ω /1000ft	inch	Amp	Amp	Amp
4	2	7	0.221	45	0.311	60	0.753	409	0.258	0.323	9	70	85	95

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

