

## 3/C FLEXIBLE CU 2000V XLPE RHH/RHW-2 PVC Power Cable With Ground VFD

Type TC-ER VFD Power Cable 2000Volt Three Conductor Flexible Copper, Cross Linked Polyethylene (XLPE) insulation RHH/RHW-2 Polyvinyl Chloride (PVC) Jacket with 3 Symmetrical Bare CU Ground 50% Minimum Tape Shield Overlap. Silicone Free




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Class I flexible ropelay stranded bare copper modified per ASTM B172
- Insulation:** Cross-Linked Polyethylene (XLPE); Type RHH/RHW-2
- Grounding Conductor:** : 3 Flexible Ropelay Stranded Bare Copper Grounds modified per ASTM B172
- Filler:** Flame & Moisture Resistant Paper Filler
- Tape Shield:** 5 mil Copper Tape Shield with a minimum of 50% Overlap for 100% Coverage
- Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 2000 Volt Type TC-ER VFD power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC® Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC® Article 336.10.

### SPECIFICATIONS:

- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors (As Applicable)
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 TC-ER
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 4
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE{R} VFD {UL} [#AWG or #KCMIL] 3/C TYPE TC-ER RHH OR RHW-2 CDRS CU GW 3 X # AWG CU T/ S50% 90{D}C PVC JACKET SUN RES DIRECT BURIAL FT4/IEEE1202 2000 VOLTS



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Diameter Over Conductor	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
	AWG/Kcmil	inch	mil	No. x AWG	mil	inch	lb/1000ft	lb/1000ft
TBD	8	0.155	70	3 x 14	60	0.749	262	343

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

† Ampacities are based on Table 310.16 of the NEC, 2020 Edition. Allowable ampacities of Insulated Conductors Rated Up to and Including 2000 Volts and Ambient Temperature of 30°C.

**Table 2 – Electrical and Engineering Data**

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	Allowable Ampacity At 75°C†	Allowable Ampacity At 90°C†
	AWG/Kcmil	inch	lb	Amp	Amp
TBD	8	9.0	396	50	55

† Ampacities are based on Table 310.16 of the NEC, 2020 Edition. Allowable ampacities of Insulated Conductors Rated Up to and Including 2000 Volts and Ambient Temperature of 30°C.

^ Copper conductors and grounds

