

# 1/C CU 5kV XLPE AIRPORT LIGHTING. SILICONE FREE

5000 Volt Non-Shielded Airport Lighting Cable, Copper Conductor With Cross-Linked Polyethylene Insulation XLPE. Meets (FAA) specification L-824 C For Underground Electrical Cable for Airport Lighting Circuits. Silicone Free



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B copper per ASTM B 3 and B8
2. **Insulation:** Cross-Linked Polyethylene XLPE. Optional colors available upon request (green, blue, red, etc.)

## APPLICATIONS AND FEATURES:

Southwire's Airport Lighting Cable meets the requirements of (FAA) L-824 C underground electrical cable for airport lighting circuits (AC 150/5345-53D), (AC 150/5345-7F). Southwire's Airport Lighting Cable is available in sizes #8 AWG through #4 AWG 7 strands. The conductors are bare annealed copper class B and covered with an abrasion, moisture, and heat resistant Cross-Linked Polyethylene XLPE insulation. The 5KV non-shielded cable is available in Black, Red and Yellow colors. Southwire Airport Lighting Cable is primarily used for series lighting circuits for runways, control systems, and other multi-purpose installations. It can be used in direct burial, conduit, or raceways. These cables are capable of operating continuously at a conductor temperature not in excess of 90°C for normal operation, 130°C for emergency and 250°C for short circuit conditions. Silicone Free.

- Cable is manufactured by Southwire Company in either Starkville, MS or Douglas, GA USA
- Cable has a warranty of 1 year from date of installation or 2 years from date of shipment whichever comes first.

## SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-96-659 (NEMA WC 71) 2001-5000 V Nonshielded Cables
- FAA L-824 C Specification Approved by (AC 150/5345-53D), (AC 150/5345-7F)

## SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE 8 AWG 5000V FAA-L824, TYPE C



**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius
	AWG	No.	mil	inch	lb /1000ft	inch
551527	4	1	110	0.460	271	3.68

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

^^ #4 AWG Stock #: 590650 Print Legend: Customer Name and Part Number: PHA74464

**Color and Stock Number**

Size	Red
#8	578099
#6	587172

