

# TGGT 250°C 300V UL 5180

Flexible Appliance and Industrial Lead Wire, Temp Rating 250°C




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** flexible stranded nickel plated, annealed copper
- Insulation:** PTFE Fluoropolymer tapes covered by wrapped fiberglass yarns
- Jacket:** A fiberglass braid jacket is applied over the insulation, then treated with a high-temperature saturant. Natural color is tan.

## APPLICATIONS AND FEATURES:

Used for the internal wiring of commercial, industrial, and household ovens as well as cooking equipment. Suited for severe hot spot locations in industrial processing.

Excellent moisture resistance, provides thermal and flame resistance, and good flexibility. High dielectric strength and low power factor without cold flow. Colors available upon request.

## SPECIFICATIONS:

- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B FT1
- RoHS-3 Complies with European Directive 2015/863

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Braid mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
C11608	16	26/.0100	8	5	0.104	13	250	5180

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Dimensions and weights for other cable configurations are available upon request.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Braid mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
C11608	16	26/.0100	0.20	0.13	2.64	19	250	5180



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services