

# MG LITE 450°C 300V UL 5360

Flexible High Temperature Lead Wire - Features Clean Stripping Insulation, Temp Rating 450°C



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Flexible stranded 27% nickel plated, annealed copper
- Insulation:** Glass reinforced phlogopite mica tapes
- Jacket:** A fiberglass braid jacket is applied over the insulation, then treated with a high-temperature saturant. Natural color is tan.

## APPLICATIONS AND FEATURES:

Used for the wiring of electrical heaters or similar high temperature equipment.

Excellent thermal and flame resistance, flexible, good chemical resistance, and produces minimal smoke when exposed to flames. Colors available upon request.

## SPECIFICATIONS:

- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B FT1
- RoHS-3 Complies with European Directive 2015/863
- Passes 70,000 BTU/Hr and the 210,000 BTU/Hr industry standard flame tests

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Braid mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
C216W1	16	26/.0100	12	7	0.100	15	450	5360

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Dimensions and weights for other cable configurations are available upon request.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Braid mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
C216W1	16	26/.0100	0.30	0.18	2.54	22	450	5360

