

MachineFLEX™ Tray Power Cable Cu 600/1000V PVC THHN TPE Jacket

Type TC-ER Machine Tray Power Cable 600/1000 Volt Copper Conductors, Polyvinyl Chloride (PVC) with nylon layer Insulation Thermoplastic Elastomer Jacket, 90°C Dry 75°C Wet -40°C Cold Impact Identification Method 4



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K, Flexible stranded bare annealed copper per ASTM B3, B172, and B174
2. **Insulation:** Polyvinyl Chloride (PVC) with nylon layer THHN
3. **Ground:** One Green Ground with Yellow Stripe THHN
4. **Jacket:** Black Thermoplastic Elastomer TPE: Other jacket colors available upon request

APPLICATIONS AND FEATURES:

Southwire's MachineFLEX™ tray power cables 600/1000 Volt conform to NFPA 79 and are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial and where superior electrical properties are desired. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC® 336.10. These cables are capable of operating continuously at the conductor temperature not in excess of 75°C in wet locations and 90°C in dry locations, 130°C for emergency overload, and 150°C for short circuit conditions. For uses in Class I, II, Division 2 hazardous locations per NEC® Article 501 and 502. Southwire's machine tray cable is ideal to power CNC machines, grinding, cutting, metal forming, buffing, bottling equipment, conveyors, processing & packaging equipment, assembly lines, control panels, food and beverage, oil sands, plant expansion, wind energy and data centers. Multiple approvals for multiple applications. Cable is rated for -40°C cold impact. Two conductor cables contain no green/yellow ground.

SPECIFICATIONS:

- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1690 Data Processing Cable (DP-1)
- UL 2277 Type WTTTC
- CSA C22.2 No. 210 Appliance wiring material products I/II A/B (Sizes 16 - 8AWG)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER
- CSA C22.2 No. 239 Control and instrumentation cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive
- NFPA 79 Electrical Standard for Industrial Machinery



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2020 Southwire Company, LLC. All Rights Reserved



SPEC 45043 DATE: 10/28/2020 23:11 UTC Rev: 3.0.00M

SAMPLE PRINT LEGEND:

Southwire XXAWG (XXmm²) XX/C PVC/Nylon Type TC-ER EXXXXX (UL) 600V 90°C Dry 75C Wet Sun Res Oil Res I/II DIR BUR -40°C OR MTW Flexing OR DP-1 OR WTTC 1000V OR AWM 20886 105°C 1000V OR c(UL) CIC/TC FT4 -- LLXXXXX CSA AWM I/II A/B 105°C 1000V -40°C FT4 -- CE RoHS -2 Made in USA

Table 1 – Physical and Electrical Data

| Stock Number | Cond. Size | Cond. Number | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Min Bending Radius | Allowable Ampacity At 60° C * | Allowable Ampacity 75°C * | Allowable Ampacity 90°C * |
|---------------|------------|--------------|---------------|------------------|------------------|------------|----------------|--------------------|-------------------------------|---------------------------|---------------------------|
| | AWG | No. | strands | mil | mil | inch | lb /1000ft | inch | Amp | Amp | Amp |
| 18 AWG | | | | | | | | | | | |
| 6773150 | 18 | 3 | 16 | 20 | 45 | 0.281 | 43 | 1.12 | 7 | 7 | 7 |
| 6775300 | 18 | 4 | 16 | 20 | 45 | 0.306 | 59 | 1.22 | 7 | 7 | 7 |
| 6773160 | 18 | 5 | 16 | 20 | 45 | 0.322 | 63 | 1.33 | 7 | 7 | 7 |
| 6775310 | 18 | 7 | 16 | 20 | 45 | 0.358 | 85 | 1.43 | 7 | 7 | 7 |
| 6775320 | 18 | 9 | 16 | 20 | 45 | 0.411 | 107 | 1.64 | 7 | 7 | 7 |
| 6775330 | 18 | 12 | 16 | 20 | 45 | 0.456 | 135 | 1.82 | 7 | 7 | 7 |
| 6773170 | 18 | 25 | 16 | 20 | 65 | 0.635 | 254 | 1.33 | 6 | 6 | 6 |
| 16 AWG | | | | | | | | | | | |
| 6775350 | 16 | 3 | 26 | 20 | 50 | 0.311 | 60 | 1.24 | 10 | 10 | 10 |
| 6775360 | 16 | 4 | 26 | 20 | 50 | 0.339 | 76 | 1.36 | 10 | 10 | 10 |
| 6773180 | 16 | 5 | 26 | 20 | 45 | 0.370 | 86 | 1.48 | 10 | 10 | 10 |
| 6773200 | 16 | 9 | 26 | 20 | 50 | 0.462 | 138 | 1.85 | 10 | 10 | 10 |
| 6773210 | 16 | 12 | 26 | 20 | 50 | 0.509 | 175 | 2.04 | 9 | 9 | 9 |
| 14 AWG | | | | | | | | | | | |
| 6772580 | 14 | 3 | 41 | 20 | 50 | 0.342 | 82 | 1.37 | 15 | 15 | 15 |
| 6772590 | 14 | 4 | 41 | 20 | 50 | 0.375 | 106 | 1.50 | 15 | 15 | 15 |
| 6530050 | 14 | 8 | 41 | 20 | 50 | 0.481 | 161 | 1.92 | 14 | 14 | 14 |
| 6772610 | 14 | 9 | 41 | 20 | 50 | 0.516 | 205 | 2.06 | 14 | 14 | 14 |
| 6773220 | 14 | 12 | 41 | 20 | 65 | 0.616 | 261 | 2.46 | 14 | 14 | 14 |
| 6772620 | 14 | 18 | 41 | 20 | 65 | 0.697 | 402 | 2.79 | 10 | 10 | 10 |
| 6772630 | 14 | 25 | 41 | 20 | 65 | 0.806 | 565 | 3.22 | 9 | 9 | 9 |
| 12 AWG | | | | | | | | | | | |
| 6772560 | 12 | 3 | 65 | 20 | 50 | 0.389 | 108 | 1.56 | 20 | 20 | 20 |
| 6775370 | 12 | 4 | 65 | 20 | 50 | 0.420 | 147 | 1.68 | 20 | 20 | 20 |
| 677538 | 12 | 5 | 65 | 20 | 50 | 0.462 | 176 | 1.85 | 20 | 20 | 20 |
| 677257 | 12 | 7 | 65 | 20 | 50 | 0.502 | 227 | 2.01 | 17 | 17 | 17 |
| 10 AWG | | | | | | | | | | | |
| 653009 | 10 | 3 | 105 | 25 | 50 | 0.462 | 161 | 2.01 | 30 | 30 | 30 |
| 6775390 | 10 | 4 | 105 | 25 | 50 | 0.502 | 206 | 2.01 | 28 | 28 | 28 |
| 677254 | 10 | 5 | 105 | 25 | 50 | 0.530 | 255 | 2.01 | 28 | 28 | 28 |
| 677255 | 10 | 7 | 105 | 25 | 60 | 0.608 | 364 | 2.43 | 24 | 24 | 24 |
| 653672 | 8 | 3 | 168 | 37 | 70 | 0.680 | 360 | 2.72 | 40 | 50 | 55 |
| 6773230 | 8 | 4 | 168 | 37 | 70 | 0.680 | 374 | 2.72 | 32 | 40 | 44 |
| 653007 | 8 | 5 | 168 | 37 | 70 | 0.766 | 441 | 3.01 | 32 | 40 | 44 |
| 6773240 | 6 | 4 | 259 | 37 | 70 | 0.760 | 556 | 3.04 | 55 | 65 | 75 |



| Stock Number | Cond. Size | Cond. Number | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Min Bending Radius | Allowable Ampacity At 60°C* | Allowable Ampacity 75°C* | Allowable Ampacity 90°C* |
|--------------|------------|--------------|---------------|------------------|------------------|------------|----------------|--------------------|-----------------------------|--------------------------|--------------------------|
| | AWG | No. | strands | mil | mil | inch | lb /1000ft | inch | Amp | Amp | Amp |
| 677325◇ | 4 | 4 | 420 | 37 | 80 | 0.969 | 830 | 3.88 | 70 | 76 | 76 |
| 652968 | 2 | 3 | 651 | 37 | 100 | 1.064 | 988 | 4.1 | 95 | 104 | 104 |
| 677326◇ | 2 | 4 | 651 | 37 | 100 | 1.196 | 1264 | 5.98 | 95 | 104 | 104 |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

† Ampacities are based on Table 310.15 (B)(16) of the NEC, 2017 Edition. Ampacities of insulated conductors rated up to and including 2000 Volts, based on ambient temperature of 30°C (86°F)

