

3/C CU 8kV 140 NLEPR 133% ARMOR-X PVC MV-105 VFD

Type MV-105 Three Conductor Copper, 140 Mills No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Continuous Corrugated Welded Armor (Armor-X), Polyvinyl Chloride (PVC) Jacket. VFD Rated.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 140 Mills No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** 3 Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
7. **Filler:** Wax paper filler
8. **Binder:** Polypropylene tape
9. **Armor:** Continuous Corrugated Welded Armor (Armor-X)
10. **Overall Jacket:** Yellow Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 8KV ARMOR-X are armored cables for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, 250°C for short circuit conditions, and -50°C for cold bend. For uses in Class I, II, and III, Division 1 and 2 hazardous locations per NEC Article 501, 502, and 503. Suitable for VFD application.

SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

{SQMTR_DUAL} SOUTHWIRE{R} ARMOR-X {NESC} MASTER-DESIGN VFD {CSA} XX KCMIL CU 140 MILS NL-EPR 8KV 133% INS. LEVEL 25%TS GW 3 X XX AWG CU CCW SUN RES 105{D}C FT4 -40{D}C LTGG HL RoHS



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Diameter Over Conductor | Diameter Over Insulation | Diameter Over Insulation Shield | Ground | Jacket Thickness ¹ | Approx. OD | Approx. Weight | Max Pull Tension | Min Bending Radius |
|--------------|------------|-------------------------|--------------------------|---------------------------------|-----------|-------------------------------|------------|----------------|------------------|--------------------|
| | AWG/Kcmil | inch | inch | inch | No. x AWG | mil | inch | lb/1000ft | lb | inch |
| TBA | 2 | 0.283 | 0.600 | 0.660 | 3 x 10 | 60 | 1.965 | 1967 | 1593 | 13.8 |
| TBA | 1 | 0.322 | 0.639 | 0.699 | 3 x 8 | 60 | 2.160 | 2289 | 2009 | 15.1 |
| TBA | 1/0 | 0.362 | 0.679 | 0.739 | 3 x 8 | 60 | 2.160 | 2558 | 2534 | 15.1 |
| TBA | 2/0 | 0.405 | 0.722 | 0.782 | 3 x 8 | 60 | 2.320 | 2930 | 3194 | 16.2 |
| TBA | 3/0 | 0.456 | 0.773 | 0.833 | 3 x 6 | 75 | 2.440 | 3527 | 4027 | 17.1 |
| TBA | 4/0 | 0.512 | 0.829 | 0.889 | 3 x 6 | 75 | 2.580 | 4075 | 5078 | 18.1 |
| TBA | 250 | 0.558 | 0.884 | 0.944 | 3 x 6 | 75 | 2.700 | 4565 | 6000 | 18.9 |
| TBA | 350 | 0.661 | 0.987 | 1.047 | 3 x 6 | 75 | 3.030 | 5788 | 8400 | 21.2 |
| TBA | 500 | 0.789 | 1.115 | 1.175 | 3 x 4 | 75 | 3.150 | 7897 | 12000 | 22.1 |
| 599684 | 750 | 0.968 | 1.303 | 1.363 | 3 x 4 | 85 | 3.710 | 10935 | 18000 | 26.0 |

All dimensions are nominal and subject to normal manufacturing tolerances
 † Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

| Cond. Size | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Shield Short Circuit Current 6 Cycles | Allowable Ampacity Directly Buried 90/105°C† | Allowable Ampacity In Air 90/105°C‡ |
|------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|---------------------------------------|--|-------------------------------------|
| AWG/Kcmil | Ω/1000ft | Ω/1000ft | MΩ*1000ft | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 2 | 0.162 | 0.203 | 0.041 | 0.042 | 0.576 + j0.489 | 0.203 + j0.042 | 2180 | 185/200 | 165/185 |
| 1 | 0.129 | 0.161 | 0.037 | 0.040 | 0.537 + j0.468 | 0.162 + j0.040 | 2307 | 210/225 | 185/210 |
| 1/0 | 0.102 | 0.128 | 0.034 | 0.039 | 0.503 + j0.447 | 0.128 + j0.039 | 2437 | 240/255 | 215/240 |
| 2/0 | 0.081 | 0.102 | 0.031 | 0.037 | 0.477 + j0.426 | 0.102 + j0.037 | 2577 | 270/290 | 245/275 |
| 3/0 | 0.064 | 0.081 | 0.028 | 0.036 | 0.455 + j0.403 | 0.081 + j0.036 | 2743 | 305/330 | 285/315 |
| 4/0 | 0.051 | 0.064 | 0.026 | 0.035 | 0.436 + j0.379 | 0.065 + j0.035 | 2925 | 350/375 | 325/360 |
| 250 | 0.043 | 0.054 | 0.025 | 0.034 | 0.423 + j0.358 | 0.055 + j0.034 | 3104 | 380/410 | 360/400 |
| 350 | 0.031 | 0.039 | 0.022 | 0.033 | 0.401 + j0.321 | 0.040 + j0.033 | 3439 | 460/495 | 435/490 |
| 500 | 0.022 | 0.028 | 0.019 | 0.031 | 0.378 + j0.283 | 0.029 + j0.031 | 3855 | 550/590 | 535/600 |
| 750 | 0.014 | 0.020 | 0.016 | 0.030 | 0.351 + j0.237 | 0.020 + j0.030 | 4467 | 665/720 | 670/745 |

* Calculations are based on 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(83) of the 2014 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(71) of the 2014 National Electrical Code (40°C Ambient Air Temperature)

