

1/C Compact CU 15kV 220 NLEPR 133% SIMpull® PVC MV-105

Type MV-105 Single Conductor Compact Copper, 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, SIMpull® Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded per ASTM B496
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35° C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE SIMpull{R} POWER CABLE MASTER-DESIGN {UL} XXX AWG CPT CU 220 MILS NL-EPR 15KV 133% INS LEVEL 25%TS MV-105 FOR CT USE SUN. RES. {NESC} PAT www.patentSW.com



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness ¹	Approx. OD	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size*
	AWG/ Kcmil	inch	inch	inch	mil	inch	lb/1000ft	lb	inch	inch
TBA	2	0.268	0.745	0.805	80	0.985	639	531	11.8	3
TBA	1	0.299	0.776	0.836	80	1.016	715	670	12.2	3
647203	1/0	0.336	0.813	0.873	80	1.053	809	845	12.6	3
TBA	2/0	0.376	0.853	0.913	80	1.093	922	1065	13.1	3.5
TBA	3/0	0.423	0.900	0.960	80	1.140	1063	1342	13.7	3.5
640921	4/0	0.475	0.952	1.012	80	1.192	1235	1693	14.3	3.5
TBA	250	0.520	1.006	1.066	80	1.246	1390	2000	15.0	4
647207	350	0.616	1.102	1.162	80	1.342	1767	2800	16.1	4
553998	500	0.736	1.222	1.282	80	1.462	2314	4000	17.5	4
TBA	600	0.813	1.330	1.390	80	1.570	2680	4800	18.8	5
561603	750	0.908	1.425	1.485	80	1.665	3210	6000	20.0	5
TBA	1000	1.060	1.577	1.637	110	1.877	4183	8000	22.5	6

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Conduit size based on 3 phase 40% fill-factor without ground

¹ Comply with ICEA S-93-639 Appendix C for jacket thickness determination

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C [†]	Allowable Ampacity In Air 90/105°C [‡]
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.203	0.053	0.052	0.573 + j0.418	0.203 + j0.051	2700	155/165	195/215
1	0.129	0.161	0.049	0.05	0.531 + j0.400	0.162 + j0.049	2827	175/185	225/250
1/0	0.102	0.128	0.045	0.048	0.496 + j0.383	0.128 + j0.047	2957	200/215	260/290
2/0	0.081	0.101	0.042	0.046	0.467 + j0.366	0.102 + j0.045	3097	230/245	300/335
3/0	0.064	0.080	0.039	0.044	0.443 + j0.346	0.081 + j0.043	3263	260/275	345/385
4/0	0.051	0.064	0.036	0.043	0.423 + j0.327	0.065 + j0.042	3445	295/315	400/445
250	0.043	0.054	0.034	0.042	0.409 + j0.309	0.055 + j0.041	3624	325/345	445/495
350	0.031	0.039	0.030	0.04	0.384 + j0.279	0.040 + j0.039	3959	390/415	550/610
500	0.022	0.028	0.026	0.037	0.361 + j0.248	0.029 + j0.037	4376	465/500	685/765
600	0.018	0.024	0.024	0.037	0.348 + j0.229	0.024 + j0.036	4655	505/544	765/855
750	0.014	0.019	0.022	0.036	0.334 + j0.210	0.020 + j0.035	4987	565/610	885/990
1000	0.011	0.015	0.020	0.035	0.315 + j0.185	0.016 + j0.034	5472	640/690	1060/1185

* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

[†] Ampacities are based on TABLE 310.60(C)(77) Detail 1. of the 2014 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

[‡] Ampacities are based on TABLE 310.60(C)(69) of the 2014 National Electrical Code (40°C Ambient Air Temperature)



Southwire



Services