

300V CU PVC PAIRS PVC SPOS Instrumentation

Type PLTC/ITC Instrumentation Cable 300 Volt Copper Conductors PVC Insulated Singles Shielded Pairs with Overall Shield SPOS. PVC Jacket Heat, Moisture, Oil and Sunlight Resistant RoHS rated for -30°C to 105°C



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B stranded bare copper per ASTM B3 and B8
- Insulation:** Twisted pair with Premium Grade Polyvinyl Chloride (PVC) Color code: Black/White alpha-numeric print alternate and inverted. 1-ONE, 2-TWO
- Drain Wire:** Tinned copper
- Twisted Shielded Pair:** 100% coverage aluminum/polyester foil shield with an individual drain wire shown in step 3
- Binder:** Mylar binder
- Overall Drain Wire:** Tinned Copper
- Overall Shielded:** 100% coverage aluminum/polyester foil shield with a drain wire as shown in step 6
- Rip Cord:** Rip cord under jacket for ease of removal
- Jacket:** Black sunlight, oil and moisture resistant Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's Instrumentation Cables Type PLTC per UL 13 and Type ITC per UL 2250 are suitable for installations as outlined in NEC Article 336 for process control and instrumentation, control circuits for operation and interconnection of protective and signaling devices and for general use in manufacturing, industrial and commercial distribution systems. Cables are constructed with 7-strand copper conductors insulated with PVC. The paired conductors are colored black, white, and alpha-numeric printed. Each pair has an aluminum polyester foil with 100% coverage and a tinned drain wire. The overall assembly is covered with an aluminum polyester foil with 100% coverage and a tinned drain wire. The cable is suited for use in cable trays, raceways, conduit, aerial (when supported with a messenger) and direct burial. The cable is rated for -30°C to 105°C and rated for Class I Div II hazardous locations, sun and oil resistant. The jacket is black PVC with a nylon ripcord for easy removal.

SPECIFICATIONS:

- UL 13 Standard for Power-Limited Circuit Cables
- UL 2250 Standard for Instrumentation Tray Cable
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- EPA 40 CFR, Part 26, Subpart C heavy metals per Table 1, TCLP method
- RoHS-2 (European Directive 2011/65/EU)
- NEC Article 336 Power and Control Tray Cable



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

SAMPLE PRINT LEGEND:

SOUTHWIRE® XX AWG XX SHIELDED PAIRS PVC/PVC TYPE PLTC/ITC E220129 (UL) 105°C SUN AND OIL RES FT4/IEEE 1202 SEQUENTIAL MARKING

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Number of Pairs	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	DC Resistance @ 25° C
	AWG/ Kcmil	pair	mil	mil	inch	lb/1000ft	inch	Ω/1000ft
TBA	18	1	15	52	0.27	46	1.08	6.66
558412	18	2	15	52	0.401	83	1.6	6.66
558414	18	4	15	65	0.49	139	1.96	6.66
591453	18	8	15	65	0.605	229	2.42	6.66
TBA	18	12	15	75	0.722	333	2.89	6.66
TBA	18	24	15	85	0.955	601	3.82	6.66
TBA	18	36	15	85	1.082	851	4.33	6.66
596818	16	2	15	52	0.443	106	1.77	4.18
558408	16	4	15	65	0.539	182	2.16	4.18
TBA	16	8	15	75	0.69	323	2.76	4.18
566925	16	12	15	75	0.799	450	3.2	4.18
566926	16	24	15	85	1.154	833	5.77	4.18
TBA	16	36	15	85	1.499	1167	7.5	4.18

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Number of Pairs	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	DC Resistance @ 25° C
	AWG/ Kcmil	pair	mm	mm	mm	lb/km	mm	Ω/km
TBA	18	1	0.38	1.32	6.86	68	27.43	21.85
558412	18	2	0.38	1.32	10.19	124	40.64	21.85
558414	18	4	0.38	1.65	12.45	207	49.78	21.85
591453	18	8	0.38	1.65	15.37	341	61.47	21.85
TBA	18	12	0.38	1.91	18.34	496	73.41	21.85
TBA	18	24	0.38	2.16	24.26	894	97.03	21.85
TBA	18	36	0.38	2.16	27.48	1266	109.98	21.85
596818	16	2	0.38	1.32	11.25	158	44.96	13.71
558408	16	4	0.38	1.65	13.69	271	54.86	13.71
TBA	16	8	0.38	1.91	17.53	481	70.10	13.71
566925	16	12	0.38	1.91	20.29	670	81.28	13.71
566926	16	24	0.38	2.16	29.31	1240	146.56	13.71
TBA	16	36	0.38	2.16	38.07	1737	190.50	13.71



Typical Electrical Specifications for Each Pair

Size	Capacitance	Inductance
AWG	µF/ft	µH/ft
18	40.66	0.0957
16	48.51	0.0895

