

3/C or 4/C CU 600V XLPE XHHW-2 CPE Control Cable With Green Ground

Type TC-ER Control Cable 600Volt Copper Conductors, Cross Linked Polyethylene (XLPE) Insulation XHHW-2 SOLONON® Chlorinated Polyethylene (CPE) Jacket with 1 Insulated Green CU Ground, Control Cable Conductor Identification Method 1 Table 2




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** 7 strands class B compressed tinned copper per ASTM B33 and ASTM B8
- Insulation:** Cross Linked Polyethylene (XLPE) XHHW-2, 30 Mils thick for all cable sizes
- Grounding Conductor:** Class B compressed stranded copper with green insulation
- Filler:** Polypropylene filler on cables with 5 or less conductors
- Overall Jacket:** Thermoplastic Chlorinated Polyethylene CPE

APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type TC-ER control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10.

SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 1 Table 2
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test

SAMPLE PRINT LEGEND:

SOUTHWIRE EXXXXX #P# (UL) [#AWG Or #kcmil] CU XHHW-2 XLPE/CPE 600V Type TC-ER For CT USE SUN. RES. For DIRECT BURIAL FT4 [-25°C] YEAR (NESC) [SEQUENTIAL FEET MARKS]



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Diameter Over Cond.	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance	AC Resistance @ 90°C	Min Bending Radius	Allowable Ampacity At 60°C *	Allowable Ampacity 75°C *	Allowable Ampacity 90°C *
	AWG	No.	inch	mil	No. x AWG	mil	inch	lb /1000ft	lb /1000ft	Ω /1000ft	Ω /1000ft	inch	Amp	Amp	Amp
16 AWG															
TBA	16	3	0.056	30	1 x 16	45	0.371	32	81	4.180	5.226	1.5	10	10	10
TBA	16	4	0.056	30	1 x 16	45	0.404	40	97	4.180	5.226	1.6	10	10	10
14 AWG															
TBA	14	3	0.070	30	1 x 14	45	0.403	51	107	2.630	3.288	1.6	14	15	15
TBA	14	4	0.070	30	1 x 14	45	0.440	64	129	2.630	3.288	1.8	14	15	15
12 AWG															
559883	12	3	0.087	30	1 x 12	45	0.445	81	146	1.660	2.075	1.8	16	20	20
TBA	12	4	0.087	30	1 x 12	45	0.487	102	177	1.660	2.075	1.9	16	20	20
10 AWG															
550639	10	3	0.111	30	1 x 10	45	0.502	130	206	1.040	1.300	2.0	24	28	30
TBA	10	4	0.111	30	1 x 10	60	0.581	162	269	1.040	1.300	2.3	24	28	30

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

† Ampacities are based on Table 310.15 (B)(16) of the NEC, 2017 Edition. Ampacities of insulated conductors rated up to and including 2000 Volts, based on ambient temperature of 30°C (86°F)

