

# 1/C CU 5kV 115 NLEPR 133% Thermoset SOLONON® LSZH-TS MV-105

Type MV-105 Single Conductor Copper, 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Thermoset SOLONON® Low Smoke Zero Halogen (LSZH-TS) Jacket, Dual Rated UL/CSA. Silicone Free




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Thermoset SOLONON® Low Smoke Zero Halogen (LSZH-TS)

## APPLICATIONS AND FEATURES:

Southwire's 5KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -25°C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. Rated for 1000 lbs./FT maximum sidewall pressure. Thermoset Solonon® jacket (XL LSZH).

## SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)



Southwire

**CABLETECH  
SUPPORT™**

Services

- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

## SAMPLE PRINT LEGEND:

{SQFTG\_DUAL} SOUTHWIRE{R} POWER CABLE SOLONON{R} MASTER-DESIGN {UL} XXX AWG CU 115 MILS NL-EPR TSET SOLONON{R} 5KV 133%/8KV 100% INS LEVEL 25%TS MV-105 ST-1 FOR CT USE {NESC} --

### Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness <sup>1</sup>	Approx. OD	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size*
	AWG/ Kcmil	inch	inch	inch	mil	inch	lb/1000ft	lb	inch	inch
TBA	2	0.283	0.550	0.610	65	0.760	462	531	9.1	2.5
TBA	1	0.322	0.589	0.649	65	0.799	531	670	9.6	2.5
TBA	1/0	0.362	0.629	0.689	65	0.839	618	845	10.1	2.5
644045	2/0	0.405	0.672	0.732	65	0.882	723	1065	10.6	2.5
TBA	3/0	0.456	0.723	0.783	80	0.963	884	1342	11.6	3
TBA	4/0	0.512	0.779	0.839	80	1.019	1048	1693	12.2	3
TBA	250	0.558	0.834	0.894	80	1.074	1194	2000	12.9	3
TBA	350	0.661	0.937	0.997	80	1.177	1556	2800	14.1	3.5
TBA	500	0.789	1.065	1.125	80	1.305	2085	4000	15.7	4
TBA	750	0.968	1.253	1.313	80	1.493	2953	6000	17.9	5
TBA	1000	1.117	1.402	1.462	80	1.642	3800	8000	19.7	5

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Conduit size based on 3 phase 40% fill-factor without ground

<sup>1</sup> Comply with ICEA S-93-639 Appendix C for jacket thickness determination

### Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C <sup>†</sup>	Allowable Ampacity In Air 90/105°C <sup>‡</sup>
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.203	0.036	0.044	0.568 + j0.512	0.203 + j0.044	2017	145/155	190/215
1	0.129	0.161	0.033	0.043	0.530 + j0.490	0.162 + j0.043	2144	170/180	225/250
1/0	0.102	0.128	0.030	0.041	0.498 + j0.468	0.128 + j0.041	2274	195/210	260/290
2/0	0.081	0.101	0.027	0.040	0.473 + j0.446	0.102 + j0.040	2414	220/235	300/330
3/0	0.064	0.081	0.025	0.039	0.452 + j0.422	0.081 + j0.039	2580	250/270	345/385
4/0	0.051	0.064	0.023	0.038	0.434 + j0.397	0.065 + j0.037	2762	290/310	400/445
250	0.043	0.054	0.022	0.037	0.423 + j0.375	0.055 + j0.037	2941	320/345	445/495
350	0.031	0.039	0.019	0.035	0.402 + j0.336	0.040 + j0.035	3276	385/415	550/615
500	0.022	0.028	0.016	0.033	0.381 + j0.296	0.029 + j0.033	3693	470/505	695/775
750	0.014	0.020	0.014	0.032	0.355 + j0.247	0.020 + j0.032	4304	585/630	900/1000
1000	0.011	0.016	0.012	0.031	0.336 + j0.216	0.016 + j0.030	4789	670/720	1075/1200



Southwire



Services

\* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(77) Detail 1. of the 2020 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(69) of the 2020 National Electrical Code (40°C Ambient Air Temperature)

