

# 1/C CU 35kV 345 NLEPR 100% SIMpull® PVC MV-105

Type MV-105 Single Conductor Copper, 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level, Tape Shield, SIMpull Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
- Conductor Shield:** Semi-conducting cross-linked copolymer
- Insulation:** 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% Insulation Level,
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
- Overall Jacket:** Polyvinyl Chloride (PVC)

## APPLICATIONS AND FEATURES:

Southwire's 35KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

## SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AIEC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

## SAMPLE PRINT LEGEND:

{SQFTG\_DUAL} SOUTHWIRE SIMpull{R} POWER CABLE MASTER-DESIGN {UL} XXX KCMIL CU 345 MILS NL-EPR 35KV  
 100% INS LEVEL 25%TS MV-105 FOR CT USE ST1 SUN RES (NESC) -- {CSA} 500 KCMIL CU 8.76mm (345 mils) NL-EPR 35KV  
 100% INS LEVEL 25%TS SR TC-ER 105{D}C FT4 -25{D}C LTDD -- PAT www.patentSW.com -- RoHS

### Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Diameter Over Conductor | Diameter Over Insulation | Diameter Over Insulation Shield | Jacket Thickness <sup>1</sup> | Approx. OD | Approx. Weight | Max Pull Tension | Min Bending Radius | Conduit Size* |
|--------------|------------|-------------------------|--------------------------|---------------------------------|-------------------------------|------------|----------------|------------------|--------------------|---------------|
|              | AWG/Kcmil  | inch                    | inch                     | inch                            | mil                           | inch       | lb/1000ft      | lb               | inch               | inch          |
| 555839       | 1/0        | 0.362                   | 1.089                    | 1.149                           | 80                            | 1.329      | 1064           | 845              | 15.9               | 4             |
| 555847       | 2/0        | 0.405                   | 1.132                    | 1.192                           | 80                            | 1.372      | 1185           | 1065             | 16.5               | 4             |
| 555854       | 3/0        | 0.456                   | 1.183                    | 1.243                           | 80                            | 1.423      | 1336           | 1342             | 17.1               | 4             |
| 555862       | 4/0        | 0.512                   | 1.239                    | 1.299                           | 80                            | 1.479      | 1520           | 1693             | 17.7               | 5             |
| 555870       | 250        | 0.558                   | 1.294                    | 1.354                           | 80                            | 1.534      | 1684           | 2000             | 18.4               | 5             |
| 551986       | 350        | 0.661                   | 1.397                    | 1.457                           | 80                            | 1.637      | 2082           | 2800             | 19.6               | 5             |
| 555888       | 500        | 0.789                   | 1.525                    | 1.585                           | 110                           | 1.825      | 2753           | 4000             | 21.9               | 5             |
| 957316       | 750        | 0.968                   | 1.713                    | 1.773                           | 110                           | 2.013      | 3696           | 6000             | 24.2               | 6             |
| 608992       | 1000       | 1.117                   | 1.862                    | 1.922                           | 110                           | 2.162      | 4602           | 8000             | 25.9               | 6             |
| 585498       | 1250       | 1.250                   | 2.000                    | 2.060                           | 110                           | 2.30       | 5525           | 8000             | 28                 |               |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Conduit size based on 3 phase 40% fill-factor without ground

<sup>1</sup> Comply with ICEA S-93-639 Appendix C for jacket thickness determination

### Table 2 – Electrical and Engineering Data

| Cond. Size | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance* | Positive Sequence Impedance* | Shield Short Circuit Current 6 Cycles | Allowable Ampacity In Duct 90/105°C <sup>†</sup> | Allowable Ampacity In Air 90/105°C <sup>‡</sup> |
|------------|----------------------|----------------------|-----------------------------|----------------------------|--------------------------|------------------------------|---------------------------------------|--|---|
| AWG/Kcmil  | Ω/1000ft             | Ω/1000ft             | MΩ*1000ft                   | Ω/1000ft                   | Ω/1000ft                 | Ω/1000ft                     | Amp                                   | Amp  | Amp   |
| 1/0        | 0.102                | 0.128                | 0.059                       | 0.052                      | 0.478 + j0.307           | 0.128 + j0.052               | 3771                                  | 200/215  | 260/290   |
| 2/0        | 0.081                | 0.101                | 0.055                       | 0.050                      | 0.448 + j0.294           | 0.102 + j0.050               | 3910                                  | 230/245  | 300/330   |
| 3/0        | 0.064                | 0.080                | 0.051                       | 0.048                      | 0.422 + j0.280           | 0.081 + j0.048               | 4076                                  | 260/275  | 345/380   |
| 4/0        | 0.051                | 0.064                | 0.048                       | 0.046                      | 0.400 + j0.265           | 0.065 + j0.046               | 4259                                  | 295/315  | 395/445   |
| 250        | 0.043                | 0.054                | 0.045                       | 0.045                      | 0.385 + j0.252           | 0.055 + j0.045               | 4438                                  | 325/345  | 440/490   |
| 350        | 0.031                | 0.039                | 0.040                       | 0.043                      | 0.360 + j0.229           | 0.040 + j0.042               | 4773                                  | 390/415  | 545/605   |
| 500        | 0.022                | 0.028                | 0.036                       | 0.041                      | 0.335 + j0.205           | 0.029 + j0.041               | 5189                                  | 465/500  | 680/755   |
| 750        | 0.014                | 0.019                | 0.031                       | 0.039                      | 0.309 + j0.176           | 0.020 + j0.038               | 5801                                  | 565/610  | 870/970   |
| 1000       | 0.011                | 0.015                | 0.028                       | 0.037                      | 0.291 + j0.158           | 0.016 + j0.037               | 6285                                  | 640/690  | 1040/1160                                       |
| 1250       | 0.009                | 0.013                | 0.025                       | 0.036                      | 0.277 + j0.143           | 0.014 + j0.036               | 6734                                  | 715/770  | 1210/1350                                       |

\* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

<sup>†</sup> Ampacities are based on TABLE 310.60(C)(77) Detail 1. of the 2020 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

<sup>‡</sup> Ampacities are based on TABLE 310.60(C)(69) of the 2020 National Electrical Code (40°C Ambient Air Temperature)



**Southwire**



Services